








RoHS
Compliant
2011/65/EU



NO.	ASSIGNMENT
1#	DAT2
2#	CD/DAT3
3#	CMD
4#	VDD
9#	CD
5#	CLK
6#	VSS
7#	DATO
8#	DAT1



(RECOMMENDED/P.C.B)HOLE LAYOUT

COMPONENT SIDE VIEW TOLERANCE: ± 0.05


SMT SOLDER AREA.

NO PATTERN AREA

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES:

1. MATERIAL:
1-1.Insulator: High Temperature Thermoplastic,UL 94V-0
1-2.Contact: Copper ALloy
2. PLATING:
2-1.Contact: Plated 30u" Ni Overall,Contact area gold-plated G/F,
Plated 80u" Sn Over Ni On Solder Area
- 3.ELECTRICAL REQUIREMENTS:
3-1.RATED CURRENT: 0.5A
3-2.Voltage Rating :125V AC/DC
3-3.Ambient Temperature Range : $-20^{\circ}\text{C} \sim +60^{\circ}\text{C}$
3-4.Storage Temperature Range : $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$
3-5.Ambient Humidity Range :95% R.H. Max.
3-6.Contact Rasisstance:100m max. Ω
3-7.Insulation Resistance:1000M min./500VDC Ω
3-8.Mating Cycles: 5000 Insertions
3-9.产品耐温温度: $260+0/-5^{\circ}\text{C}$



PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DATO	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)
9	CD	CD	CD

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:	TITLE	TF卡座外焊9PIN 贴片式 1.85H 鱼叉脚镀镍 无定位柱
X : ± 0.30	X : $\pm 2^{\circ}$	DWN	xiong
X.X : ± 0.20	X.X : $\pm 1^{\circ}$	CHKD	lee
X.XX : ± 0.10		APVD	wang
		SCALE:1:1	UNIT: mm
		SIZE: A4	SHEET:10F 1
		REV: A4	CUSTOMER COPY