




SECTION : P-P



N = Number of poles
 Dim A=Nx3.81+1.39
 Dim B=(N-1)x3.81
 Dim C=Nx3.81+5.19
 Dim D=Nx3.81+10.39

	Dim A	Dim B	Dim C	Dim D
2-6p	±0.15	±0.15	±0.15	±0.15
7-12p	±0.20	±0.20	±0.20	±0.20
13-18p	±0.30	±0.30	±0.30	±0.30
19-24p	±0.35	±0.35	±0.35	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.11.13	The design is changed from the round hole to hexagonal hole	Jacke
△	2011.02.25	The wire is changed from 14-30(AWG) to 14-28(AWG)	Aaron
△	2011.02.25	Add is cULus	Aaron
△	2012.04.07	Change the structure of nut and add the glue process	Venter
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Material:

- Item a Clamp: Brass Ni plated
- Item b Male contact pin: Brass, Tin plated.
- Item c Terminal screw: Steel Zinc plating
- Item d With flange nut: Brass M2.5
- Item e Terminal housing: Thermoplastic (UL94V-0)
- Item f Terminal cover: Thermoplastic (UL94V-0)
- Item g Terminal(track): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating:300V
- Current rating:8A
- Wire range:
- △ ● Solid wire(AWG):14-28
- △ ● Stranded wire(AWG):14-28
- Torque(Lb-In):2.17
- Screw: M2
- Wire strip length:6 mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C

△ ● Safety Approval: cULus

V5 xx 31 x 3 xxxxx G

No. OF POLES

- 03 3 CONTACTS
- 04 4 CONTACTS
-
- 24 24 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

G RoHS compliant (lead<4%)
 In copper Alloy
 0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by
 customer request.
 please contact sales
 department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	V5 3.81 mm W/ Flange Dinrail holder A type Series						
PART NO.	V5xx31x3xxxxG			DWG NO.	8V50104		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Venter 2012.04.07	Venter 2012.04.07		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
						X.XX	±0.10
				SHEET: 01/01	REV.: E	X°	±1°