







PCB LAYOUT

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim A	10	15	20	25	30	35	40	45	50	55	60	65
Dim B	5	10	15	20	25	30	35	40	45	50	55	60
TOL	±0.10				±0.15					±0.20		
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	70	75	80	85	90	95	100	105	110	115	120	
Dim B	65	70	75	80	85	90	95	100	105	110	115	
TOL	±0.20		±0.25					±0.30				



SIGN	DATE	DESCRIPTION	APPROVER
	01/10'09	The design is changed	Jacke
	04.20'09	The current rating and operating temperature are changed	Jacke
	2010.01.12	Add cULus standard	Jacke
	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!!			

Materials

Item a Terminal body;Thermoplastic (UL94V-0)

Item b Female contact:PhBz(CuSn),Tin plated

Item c Terminal cover:Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Δ Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Δ Safety Approval: us

V7 xx 7 1 x 1 xxxx G

No. OF POLES

02 2 CONTACTS

03 3 CONTACTS

1000

24 24 CONTACTS

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

— G: Pb<40000ppm

— 0000: “@” Logo (Standard)

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 5.0 Series Right angle						
PART NO.		V7xx71x1xxxxG			DWG NO.	8V70201		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacke 2010.03.31	Jacke 2010.01.12		UNIT: mm		X.	±0.5
					SCALE: 2:1		X.X	±0.3
				SHEET: 01/01	REV.: E		X.XX	±0.1
							X°	±1°