

APPEARANCE



SOD-523 (Top View)

PIN CONFIGURATION



Pin configuration (Top view)

Descriptions

The APES12H15-52 is a Uni-directional transient voltage suppressor (TVS) to protect sensitive electronic components from electrostatic discharge (ESD). It is particularly well-suited for cellular phones, PMP , MID, PDA, digital cameras and other electronic quipment. The APES12H15-52 is safely dissipating ESD strikes to meet the ESD immunity testing of IEC61000-4-2 ($\pm 30KV$).


The APES12H15-52 is available in SOD-523 package. Standard products are Pb-free and Halogen-free.

Order information

Device	Package	Shipping
APES12H15-52	SOD-523	3000/Tape&Reel

Electrical Parameters (T=25°C)

Symbol	Parameter
V_{RWM}	Reverse Stand-off Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{BR}	Reverse Breakdown Voltage @ I_T
I_T	Test Current
I_{PP}	Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
I_F	Forward Current
V_F	Forward Voltage @ I_F




Absolute maximum ratings

Parameter	Symbol	Rating	Unit
Peak pulse power (tp = 8/20μs)	Ppk	385	W
Peak pulse current (tp = 8/20μs)	I _{PP}	15	A
ESD according to IEC61000-4-2 air discharge	V _{ESD}	±30	kV
ESD according to IEC61000-4-2 contact discharge		±30	kV
Junction temperature	T _J	150	℃
Operating temperature	T _{OP}	-55~125	℃
Storage temperature	T _{STG}	-55~150	℃


Electronics characteristics (Ta=25℃)

Parameter	Symbol	Condition	Min	Typ	Max	Units
Reverse Stand-off Voltage	VRWM				12	V
Reverse Breakdown Voltage	VBR	I _t =1mA	13.5		15.5	V
Reverse Leakage Current	I _R	VRWM=12V			0.1	uA
Clamping Voltage	V _C	I _{pp} =15A, tp=8/20us			26	V
Junction Capacitance	C _j	V _R =0V, f=1MHz		80		pF


Typical characteristics (Ta=25°C)



Pulse Waveform (8/20us)




Pulse Derating Curve



ESD Clamping(8kV Contact Discharge)

PACKAGE OUTLINE DIMENSIONS(SOD-523)



UNIT	A	b _p	C	D	E	H _E	V	
mm	0.68 0.58	0.4 0.3	0.135 0.100	1.25 1.15	0.85 0.75	1.7 1.5	0.1	5°

Note:
This recommended land pattern is for reference purpose only.