


APPEARANCE



DFN1006-2L (Bottom View)

PIN CONFIGURATION



Pin configuration (Top view)

Descriptions

The APED5.0M4.0-10 is a Bi-directional transient voltage suppressor (TVS) to protect sensitive electronic components from electrostatic discharge (ESD). It is particularly well-suited for cellular phones, PMP , MID, PDA, digital cameras and other electronic quipment. The APED5.0M4.0-10 is safely dissipating ESD strikes to meet the ESD immunity testing of IEC61000-4-2 ($\pm 25\text{KV}$).


The APED5.0M4.0-10 is available in DFN1006-2L package. Standard products are Pb-free and Halogen-free.

Order information

Device	Package	Shipping
APED5.0M4.0-10	DFN1006-2L	10000/Tape&Reel

Electrical Parameters (T=25°C)

Symbol	Parameter
VRWM	Reverse Stand-off Voltage
IR	Reverse Leakage Current @ VRWM
VBR	Reverse Breakdown Voltage @ IT
IT	Test Current
IPP	Reverse Peak Pulse Current
VC	Clamping Voltage @ IPP




Absolute maximum ratings

Parameter	Symbol	Rating	Unit
Peak pulse power ($t_p = 8/20\mu s$)	Ppk	45	W
Peak pulse current ($t_p = 8/20\mu s$)	I _{PP}	4.0	A
ESD according to IEC61000-4-2 air discharge	V _{ESD}	±25	kV
ESD according to IEC61000-4-2 contact discharge		±25	kV
Junction temperature	T _J	150	°C
Operating temperature	T _{OP}	-55~125	°C
Storage temperature	T _{STG}	-55~150	°C


Electronics characteristics (Ta=25°C)

Parameter	Symbol	Condition	Min	Typ	Max	Units
Reverse Stand-off Voltage	VRWM				5.0	V
Reverse Breakdown Voltage	VBR	I _t =1mA	5.6	6.1	8.0	V
Reverse Leakage Current	I _R	VRWM=±5.0V			0.1	uA
Clamping Voltage	VC	I _{pp} =4.0A, t _p =8/20us			12	V
Junction Capacitance	C _j	VR=0V, f=1MHz		12		pF


Typical characteristics (Ta=25°C)



Pulse Waveform (8/20us)




Pulse Derating Curve



ESD Clamping(8kV Contact Discharge)

PACKAGE OUTLINE DIMENSIONS(DFN1006-2L)



Note:
This recommended land pattern is for reference purpose only.