






CIRCUIT - 1 POSITION

P.C. LAYOUT





ISOMETRIC



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT RATINGS: 25mA @24VDC. (Switch)
100mA @50VDC. (Carry)
- ▲5. CONTACT MATERIAL:
CONTACTS: (MOVABLE) COPPER w/GOLD PLATE
TERMINALS: BRASS w/GOLD PLATE
6. INSULATION RESISTANCE: 100 MEGA-OHMS MIN. @500VDC
7. CONTACT RESISTANCE: 50 MILLI-OHMS MAX @2-4VDC @100mA INITIAL
8. OPERATING TEMP: -40°C TO +85°C
- ▲9. PACKAGE: 200 PCS PER TUBES,
WITH ALL POLES IN THE "OFF" POSITION.
10. MECHANICAL LIFE: 2,000 CYCLES
11. 2002/95/EC (ROHS) COMPLIANT.
12. ▲ DENOTES CRITICAL PARAMETER.

(NO TAPE)



TITLE KAJ01SGGT

B	19599	REMOVED E-SWITCH LOGO	1/18/11	BGL
A	17978	RELEASED FOR PRODUCTION	2/22/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				

SCALE 4:1	DATE 2/22/2008	DR BLR	DWG W825373	REV B
-----------	----------------	--------	-------------	-------