



EVCS1806-S-X-Y-00A

3kV_{RMS} Isolated Hall-Effect Current Sensor Evaluation Board

DESCRIPTION

The EVCS1806-S-X-Y-00A is an evaluation board designed to demonstrate the capabilities of the MCS1806GS-X-Y series, which are high-accuracy, linear Hall-effect current sensors for AC or DC current sensing. The Hall array is differential, which cancels out stray magnetic field. The MCS1806GS-X-Y series provides two power supply options (3.3V or 5V) and six full current ranges of 5A to 50A to optimize accuracy in different applications.

The output voltage (V_{OUT}) is proportional to the applied current flowing through the primary conductor. The galvanic isolation between the primary conductive path pins and the sensor leads allows the MCS1806GS-X-Y to replace optoisolators or other expensive isolation devices.

PERFORMANCE SUMMARY


Specifications are at $T_A = 25^\circ\text{C}$, unless otherwise noted.

Parameters	Conditions	Value
Supply voltage (V_{CC})		3.3V or 5V
Maximum primary applied current (I_{P_MAX})		Six options: $\pm 5\text{A}$ to $\pm 50\text{A}$
Output voltage (V_{OUT})		$0.5 \times V_{CC} + \text{Sens}_{(TYP)} \times I_P^{(1)}$
Total accuracy	I_P from 10% $\times I_{P_MAX}$ to I_{P_MAX}	$<2.5\%$

Note:

1) $\text{Sens}_{(TYP)}$ is the symbol for “typical sensitivity.”

EVCS1806-S-X-Y-00A EVALUATION BOARD



LxWxH (58mmx58.5mmx12mm)
2 Layers

Board Number	MPS IC Number
EVCS1806-S-X-Y-00A	MCS1806GS-X-Y

EVALUATION BOARD BASIC INFORMATION

Evaluation Board PN	Typical VCC Supply Voltage (V)	Rated Primary Current Range (A)	Typical Sensitivity (mV/A)
EVCS1806-S-3-05-00A	3.3	±5	264
EVCS1806-S-3-10-00A		±10	132
EVCS1806-S-3-20-00A		±20	66
EVCS1806-S-3-30-00A		±30	44
EVCS1806-S-3-40-00A		±40	33
EVCS1806-S-3-50-00A		±50	26.4
EVCS1806-S-5-05-00A	5	±5	400
EVCS1806-S-5-10-00A		±10	200
EVCS1806-S-5-20-00A		±20	100
EVCS1806-S-5-30-00A		±30	66
EVCS1806-S-5-40-00A		±40	50
EVCS1806-S-5-50-00A		±50	40

QUICK START GUIDE

1. Preset DC power supply to 3.3V or 5V.
2. Turn off the power supply.
3. Connect the DC power supply terminals to:
 - a. Positive (+): VCC
 - b. Negative (-): GND
4. Connect the current source terminals to:
 - a. Positive (+): IP+
 - b. Negative (-): IP-
5. Turn on the DC power supply and current source, then measure the output result via the VOUT pin.
6. C4 determines the sensor's bandwidth. A lower bandwidth results in reduced output voltage ripple noise.

EVALUATION BOARD SCHEMATIC




Figure 1: Evaluation Board Schematic


EVCS1806-S-X-Y-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer PN
1	C1	0.1μF	Ceramic capacitor, 16V, X7R	0603	Murata	GRM188R71C104KA01D
1	C2	4.7μF	Ceramic capacitor, 16V, X7R	0805	Murata	GCM21BR71C475KA73L
1	C3	NC				
1	C4	NC				
2	IP+, IP-	4 pins	Screw terminal	DIP	Keystone Electronics	8191K-ND
1	U1	MCS1806GS-X-Y	Linear Hall-effect current sensor with ±2.5% accuracy	SOIC-8	MPS	MCS1806GS-X-Y


EVB TEST RESULTS

Performance waveforms are tested on the EVCS1806-S-5-50-00A evaluation board. $V_{CC} = 5V$, C3 open, C4 open, $T_A = 25^\circ C$, unless otherwise noted.


DC Current Status

 $I_P = 50A$



DC Current Status

 $I_P = -50A$



Start-Up through VCC

 $I_P = 50A$



Shutdown through VCC

 $I_P = 50A$


Step-Up Current



Step-Down Current

 $I_P = 50A$


PCB LAYOUT




Figure 2: Top Silk




Figure 3: Top Layer




Figure 4: Bottom Layer



REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	12/8/2022	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.