

KNSCHA

Empowering The World

广东科尼盛电子科技有限公司

KNSCHA ELECTRONICS CO.,LIMITED

IATF16949:2016

ISO9001:2015

ISO14001:2015

部品规格书 APPROVE SHEET

客 户 名 称 Customer Name	
产 品 名 称 Product Name	贴片型铝电解电容器 SMD Aluminum Electrolytic Capacitors
客 户 料 号 Customer P/N	
科 尼 盛 料 号 KNSCHA P/N	225RV0054
型 号 规 格 Product Type	10uF ±20% 100V 105°C@2000Hours SMD,D6.3xL7.7mm KNS RVT Series
日 期 Date	2025年03月15日

制 造 Manufacture	
核 准 APPROVAL	制 作 PREPARED
王 伟	刘 国 华

客 户 承 认 栏 CUSTOMER APPROVED		
核 准 APPROVED	确 认 CHECKED	经 办 DESIGNED

④ 网址: www.knscha.com ④ 邮箱: sales@knscha.com

④ 电话: 0769-81035570 83698067 ④ 传真: 0769-83861559

④ 营业中心: 东莞市寮步镇香市科技产业园松湖智谷研发中心A3栋8层
8th floor,Building A3,Songshan Lake Intelligent Valley,Dongguan,
Guangdong,China

④ 总部基地: 广东省东莞市东坑镇农横路7号汇金展拓科技园
Building 3, No.7 Nongheng Road, Dongkeng Town, Dongguan,
Guangdong Province, China

④ 杭州分公司: 浙江省杭州市余杭区临平余之城1栋20楼
④ 厦门办事处: 福建省厦门市集美区厦门软件园三期F12栋901-8室

KNSCHA

Empowering The World

KNSCHA ELECTRONICS CO., LIMITED

IATF16949:2016 ISO9001:2015 ISO14001:2015

Aluminum Electrolytic Capacitors

- Source Manufacturer
- 25+ Years Experience
- 7X24 Hours Online Service



Film Capacitors

- Source Manufacturer
- 10+ Years Experience



c **UL** [®] US

EN ¹⁰

DE

CQC

K

TÜV

KNSCHA

Empowering The World



+86(769)83698067

www.knscha.cn

8th floor,Building A3,Songshan Lake Intelligent Valley,Dongguan,Guangdong,China

Building 3, No.7 Nongheng Road, Dongkeng Town, Dongguan, Guangdong Province, China

+86(769)83861559

cathy@knscha.com

KNSCHA ELECTRONICS CO.,LIMITED

IATF16949:2016 ISO9001:2015 ISO14001:2015

广东科尼盛电子科技有限公司
KNSCHA ELECTRONICS CO.,LIMITED

IATF16949:2016 ISO9001:2015 ISO14001:2015

[illegible]

RVT

105℃,2000Hrs,Standard Series

特性/ Features

105℃, 2000 hours assured.
Available for high density surface mounting.
High stability and reliability.




表1 规格表 Specifications

Item	Condition		Specifications							
Category Temperature Range(℃)	※		-40℃ ~ +105℃							
Capacitance Tolerance (%)	120Hz, 20℃		±20%							
Rated Voltage (v)	※		6.3	10	16	25	35	50	63	100
Dissipation Factor (tanδ)	120Hz, 20℃ (Max.)	tanδ	0.30	0.24	0.20	0.18	0.16	0.14	0.14	0.14
		Notes	Exceeding 1,000uF, +0.02 every 1,000uF							
Leakage Current (LC)	After 2 minutes, 20℃ (uA, Max.)		0.01CV or 3uA, whichever is greater.							
Low Temperature Characteristics	Impedance Ratio (Max.)	Z _{25℃} /Z _{+20℃}	5	4	3	2	2	2	2	2
		Z _{-40℃} /Z _{+20℃}	10	8	6	4	3	3	3	3
Endurance	105℃, Rated Voltage Applied (With the rated ripple current)	Hours	2,000							
		ΔC/C	Within ±30% of initial value							
		tanδ	300% or less of the initial specified value							
		LC	The initial specified value or less							
Shelf life	105℃	Hours	1,000							
		Other Items	same as those for the endurance.							

表2 外形尺寸 Dimensions(mm)




表3 纹波电流与频率补正系数 Ripple Current and Frequency Multipliers

Frequency (Hz) Capacitance (uF)	50	120	1k	10k up
Under 100	0.70	1.00	1.35	1.50
100 ~ 2200uF	0.80	1.00	1.20	1.30

表4 标准品一览表 Standard Size

uF	6.3v (0J)		10v (1A)		16v (1C)		25v (1E)		35v (1V)		50v (1H)		63v (1J)		100v (2A)	
	ΦD x L	R.C.	ΦD x L	R.C.	ΦD x L	R.C.	ΦD x L	R.C.	ΦD x L	R.C.	ΦD x L	R.C.	ΦD x L	R.C.	ΦD x L	R.C.
1.0											4x5.7	7	4x5.7	7	4x5.7	7
2.2											4x5.7	11	4x5.7	11	4x5.7	9
3.3									4x5.7	13	4x5.7	13	5x5.7	13	5x5.8	14
4.7							4x5.7	13	4x5.7	14	4x5.7	13	5x5.7	16	5x5.8	16
6.8							4x5.7	14	4x5.7	14	4x5.7	14	5x5.7	17	6.3x5.7	21
10					4x5.7	18	4x5.7	14	4x5.7	14	5x5.7	18	5x5.7	19	6.3x5.7	35
22			4x5.7	20	4x5.7	20	4x5.7	19	5x5.7	30	6.3x5.7	42	6.3x5.7	40	6.3x7.7	60
33	4x5.7	22	4x5.7	22	4x5.7	22	4x5.7	22	5x5.7	34	6.3x5.7	45	6.3x7.7	51	8x10.5	84
47	4x5.7	25	4x5.7	25	5x5.7	31	5x5.7	35	6.3x5.7	50	6.3x7.7	60	6.3x7.7	63	8x10.5	90
68	5x5.7	33	5x5.7	30	6.3x5.7	48	6.3x5.7	48	6.3x7.7	70	6.3x7.7	63	8x10.5	112	10x10.5	133
100	4x5.7	25	5x5.7	40	5x5.7	31	6.3x5.7	48	6.3x5.7	50	6.3x7.7	63	8x10.5	125	10x10.5	155
150	5x5.7	39	6.3x5.7	53	6.3x5.7	60	6.3x7.7	91	6.3x7.7	84	8x10.5	120	8x10.5	135	10x12.5	180
220	6.3x5.7	67	6.3x5.7	70	6.3x7.7	110	6.3x7.7	120	8x10.5	190	8x10.5	155	10x10.5	205		
330	6.3x7.7	105	6.3x7.7	105	6.3x7.7	120	8x10.5	175	10x10.5	220	10x10.5	170	10x12.5	225		
470	6.3x7.7	120	6.3x7.7	130	8x10.5	195	8x10.5	220	8x10.5	225						
680	8x10.5	210	8x10.5	210	10x10.5	240	10x10.5	240	10x10.5	245						
1000	8x10.5	230	8x10.5	240	10x10.5	255	10x10.5	280	10x10.5	320						
1500	10x10.5	315	10x10.5	260	10x12.5	390	10x12.5	375								
2200	10x10.5	350														

Note1: Case size ΦD x L(mm), ripple current (mA, rms) at 105℃, 120Hz.
Note2: Produce custom product too, which are not found in these tables.