










RECOMMENDED PCB LAYOUT (COMPONENT SIDE VIEW)
EMPFOHLENES LEITERPLATTEN-LAYOUT (BESTUECKUNGSSEITE)
TOL ± 0.05 mm unless noted




RECOMMENDED PANEL CUTOUT
EMPFOHLENER FRONTPLATTEN-AUSSCHNITT



CONTACT DESIGN



1:1



NOTE 1: RoHS COMPLIANT

PART NO. IDENT. NR.	TRANSMISSION REQUIREMENT ÜBERTRAGUNGSANFORDERUNG	CONTACT FINISH KONTAKTOBERFLÄCHE	OPERATION TEMPERATURE BETRIEBSTEMPERATUR
133934	CAT 5	50 μ inAu	0 to +70°C
203512	CAT 5	30 μ inAu	-40° to +85°C
133184	CAT 5	30 μ inAu	0 to +70°C
133183	CAT 3/4	30 μ inAu	0 to +70°C
Information:		Tolerances x.xx = ± 0.25 mm	Scale 2:1
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		All Dimensions in mm [in]	Designation
Subject to modification without prior notice. Drawing will not be updated.		www.ERNI.com	MOD JACK - MJHV 8P8C, 1X1, VERTICAL
j		13.01.2020	133819
Index		Date	I
			A3
			Class MJ