

SPECIFICATION FOR APPROVAL

承 認 書

CUSTOMER

客戶名稱：

NUMBER

编号: Y-6032305

PART NO.

品 名：SMD POWER INDUCTORS

QUANTITY

數量：10PCS

DESCRIPTION

型 號： CDH129 – 330M

DATE

日期：2024-05-22

CUSTOMER PART NO.

客戶料號：

NOTE

注解：

APPROVAL SIGNATURE

客戶承認簽章

Approved By 核 准	Checked By 审 查	Drawn By 制 作
李 庆 辉	刘 志 坚	劳 水 花

深圳市柯爱亚电子有限公司

Shenzhen Ceaiya Electronics Co., Ltd.

深圳地址：深圳市龙华区高新技术开发区捷顺科技中心 B706

东莞地址：东莞清溪镇青滨东路 105 号力合智造中心 10 栋一单元

Http://www.szceaiya.com

Tel: 0769-89135516

Fax: 0769-89135519



SPECIFICATIONS

TYPE:


CDH129-330M

1. Scope

This specification apply for CDH129 of power inductors

2. Appearance

2-1.Dimensions(mm)



A	12.5mm(Max)
B	9.8mm(Max)
C	5.0 mm
D	2.0 mm

Font size: Width 7.1*High3 Song ti

* Dimension without tolerance is approx.

3. Coils Specification

3-1. Connection (Bottom View)



“S” is winding start

3-2. Turns and Wire

Terminal	S-F
Turns	19.5 Ts
Wire	0.38mm*2P G1 P180

* Winding Turns are approx.

LEAD-FREE

RoHS

Compliance

Note :

Spec. No.

Y-6032305

2/6

SPECIFICATIONS

TYPE:

CDH129-330M

3-3. Electronical characteristics

Item	Specifications	Measuring Conditions	Measuring Instrument
Inductance	33 μ H \pm 20% Within	1KHz/0.25V	CH1062
D.C.R	55m Ω Max	25 $^{\circ}$ C	HIOKI 3540
I.D.C※	4A	1KHz/0.25V	CH1062&Chroma1320

※ This indicates the value of current when the inductance is 35% lower than its initial value at D.C superposition or D.C current when temperature rise $\Delta T=40^{\circ}\text{C}$


4. General Characteristics

4-1. Storage Temperature range : $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

4-2. Operating temperature range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$ (Including coil's self temperature rise)


4-3. External appearance : No external defects can be found in the visual inspection.

4-4. Electrode strength : No electrode detachment should be found when the device is pushed in two directions of X and Y with the force of 5.0N for 10 ± 2 seconds after soldering between copper plate and the electrodes.
(Refer to figure at right)



4-5. Vibration test : Inductance deviation is within $\pm 10\%$ after 1 hour sweeping vibration in each three directions, namely, forward and backward, up and down, right and left. The frequency is $10 \sim 55 \sim 10\text{Hz}$ and the amplitude of 1 minute cycle is 1.5mm PP.

4-6. Recommended reflow condition :



Note :

Spec. No.

Y-6032305

3/6


SPECIFICATIONS

TYPE:

CDH129-330M

4-7.Humidity test : Inductance deviation is within $\pm 5.0\%$ after 96 ± 4 hours test under the condition of relative humidity of $90\sim 95\%$ and temperature of $60\pm 2^{\circ}\text{C}$, and 1 hour storage under room ambient conditions after the device is wiped with dry cloth.

5. Construction and materials



No.	Part name	Material	Ceaiya P/N
①	Drum Core	Ni-Zn Ferrite Core	(TT/WS)
②	Wire	Polyurethane enameled copper wire	3210380
③	Ring Core	Ni-Zn Ferrite Core	(TT/WS)
④	Adhesive	Epoxy Resin	7001006(007)
⑤	Electrode	Cu + Sn plating	(LC)

Note :

Spec. No.

Y-6032305


4/6

SPECIFICATIONS


TYPE:

CDH129–330M

6. TAPE DIMENSIONS:



W	24.00±0.30	P	16.0±0.10	A0	12.70±0.10	D1	ø1.50MIN
T	0.50±0.05	P0	4.00±0.10	B0	12.70±0.10	D0	ø1.50 ^{+0.10} ₋₀
E	1.75±0.10	P2	2.00±0.10	K0	9.90±0.10	F	11.50±0.10




Note:	Spec. No. Y-6032305 5/6
-------	-------------------------------

SPECIFICATIONS

TYPE:
CDH129-330M

7. TAPE REEL DIMENSIONS:



单位：毫米

Type	A	B	C	G	N	T
24mm	330	21±0.8	13±0.2	24.4	100	28.4

PACKAGING QUANTITY :
250 PCS /REEL

Note :	Spec. No. Y-6032305 6/6
--------	-------------------------------