




h : 0 : RL



SHELL SIZE	Ø A Maxi	B MINI	CAPACITY C		HEXAGON D	Tightening torque (BACKSHELL NUT)
			STANDARD	REDUCING SEAL		
08	22.50	54.00	2.5/6.5	1.50/5.00	16.00	2 Nm
10	26.70	63.20	2.50/8.00	1.50/5.00	18.50	3 Nm
12	30.15	66.70	5.00/12.00	3.00/9.00	24.00	3 Nm
14	35.10	71.50	7.00/14.00	5.00/12.00	26.00	3 Nm

MATERIAL :


Coupling Nut:Polyamid UL94 V-0
Insert:Polychloropren (CR)
Backshell :Polyamid UL94 V-0
Shell : Polyamid UL94 V-0
Coupling spring : Stainless steel
O'seal : Nitril
Contact : Brass + gold plated

PERFORMANCE CHARACTERISTICS :


Operating temperature:-40°C up to 105°C
Insulation resistance:5000 MΩ min
Test potential:1500Vrms for #20 layout
Corrosion salt spray:500 hours
Durability:250 matings and unmatings
Sealing in mated conditions:
-IP68 1 bar during 1 week : immersion under 10 m of water.
(IEC 60529)
-IP69K : exposure to high pressure water of cleaning
equipement(DIN 40050)

NOTES :

- 1-Plug,backshell and the reducing seal are delivered as a kit
The backshell already includes the standard seal.
- 2-Insert arrangements : refer to C144-UTS1-A
- 3-Colored ring to be orderd separately refer to customer drawing C006-UTS1-A



CUSTOMER DRAWING

h		12/05/11	add orientations in the part number		21774			
ISS		DATE	Latest modification - by: J.FEURPRIER		MOD N°			
Designed by: SORIN V.			Date:24/10/07		CUSTOMER DRAWING			
TITLE		PLUG WITH BACKSHELL UTS HI SEAL						
Scale 2/1				General linear Tolerances: ± 0.1		NPRDS / PROJECT UTS		
		WWW.SOURIAU.COM				This document is the property of SOURIAU It must not be reproduced or communicated without permission		
FORMAT A2		SOURIAU DRG N° C043-UTS1-A					SHEET 1 / 1	
NOT EXPORT CONTROLLED								