

P/N	Dimensions(mm)	
	A	B
WAFER-XSR0.6-2PWB	0.60	3.00
WAFER-XSR0.6-3PWB	1.20	3.60
WAFER-XSR0.6-4PWB	1.80	4.20
WAFER-XSR0.6-5PWB	2.40	4.80
WAFER-XSR0.6-6PWB	3.00	5.40
WAFER-XSR0.6-7PWB	3.60	6.00
WAFER-XSR0.6-8PWB	4.20	6.60
WAFER-XSR0.6-9PWB	4.80	7.20
WAFER-XSR0.6-10PWB	5.40	7.80
WAFER-XSR0.6-11PWB	6.00	8.40
WAFER-XSR0.6-12PWB	6.60	9.00
WAFER-XSR0.6-13PWB	7.20	9.60
WAFER-XSR0.6-14PWB	7.80	10.20
WAFER-XSR0.6-15PWB	8.40	10.80
WAFER-XSR0.6-16PWB	9.00	11.40
WAFER-XSR0.6-17PWB	9.60	12.00
WAFER-XSR0.6-18PWB	10.20	12.60
WAFER-XSR0.6-19PWB	10.80	13.20
WAFER-XSR0.6-20PWB	11.40	13.80
WAFER-XSR0.6-22PWB	12.60	14.40

Specification

- 1.Voltage rating: 30V AC/DC
 - 2.Current rating: 0.2A AC/DC
 - 3.Contact Resistance: $\leq 30\text{ m}\Omega$
 - 4.After environmental testing: $\leq 50\text{ m}\Omega$
 - 5.Insulation resistance: $\geq 100\text{m}\Omega$
 - 6.Withstanding voltage: 200 VC/minute
 - 7.Temperature range: $-25^{\circ}\text{C}\sim +85^{\circ}\text{C}$
- Suitable Wire/Cable:AWG #36 to #34,OD:0.32mm max

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:0.6mm(.024'') pitch PCB Header/Wafer R/A SMD/SMT		
			PAR	WAFER-XSR0.6-NPWB	
DECIMALS:	ANGLES:		DWN	Lucas	
.X:±0.30	±3°		CHKD	Ethan	
.XX:±0.20			APVD	Jacob	
.XXX:±0.10			SCALE1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A

Recommended P.C.B Layout
General Tolerance ± 0.05