



Technical specification:

Rated voltage: 250 V
IEC 61076-2-101

Current rating: 4 A at 40°C
IEC 61076-2-101

Insulation resistance: $\geq 100 \text{ M}\Omega$
IEC 60512

Pollution degree: 3/2
IEC 60664-1

Degree of protection: IP 67, in mated condition
IEC 60529

Temperature range: -30°C ... +85°C

Mating cycles: ≥ 100
IEC 60512-9a

Materials:

Contact: CuZn

Contact plating: Nickel, gold plated

Contact carrier: PBT GF, UL 94

Sealing connector: FPM
chassis: NBR

Counternut: CuZn, nickel plated


Socket housing: CuZn, nickel plated

Grouting: Polyurethane-resin, UL 94

Installation specification:

Recommended torque: 1-1,2 Nm

Conec installation tool: Torque wrench:
36-000200
Insert across flats 19:
36-000250




Minimum wall thickness 1,5mm,
alternativ panel cut-out d=15,3

Part no:	Description:	Pos:	Length L:	D1
43-01236	SAL - 12D - FKH4 - P5,5 - 9	4	5,5mm	Ø5,0
43-01248	SAL - 12D - FKH4 - P12 - 9	4	12mm	Ø5,0

DO NOT ALTER CAD DRAWING BY HAND

Directive 2011/65/EU RoHS compliant

Index: f 08.09.14 MG Ä5180
temperature range changed



dim. in mm

	date	name
drawn	22.10.07	Fromm
appd.	22.10.07	Burschik

CONEC®

title:

Female socket M12x1 with
dip solder, backmounting, PG9,
Industrial Ethernet

dwg no:

43K1A560

part no:

see table

general tolerance: 0 $\pm 0,50\text{mm}$
0,0 $\pm 0,25\text{mm}$
0,00 $\pm 0,10\text{mm}$

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND
MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH