



DATA SHEET

BAS16L

- ◇Fast switching devices
- ◇Low Reverse Leakage Current
- ◇ ROHS Compliant
- ◇ UL-94 V-0 / Green EMC
- ◇Matte Tin Lead finish (Pb-Free)

Device Marking Code	
BAS16L	<u>S2</u>

Pin & Polarity



Maximum Ratings (Ta = 25 °C)


Symbol	Parameter	Value	Units
V_{RSM}	Non-Repetitive Peak Reverse Voltage	100	V
V_{RRM}	Peak Repetitive Reverse Voltage	75	V
V_{RWM}	Working Peak Reverse Voltage		
V_R	Dc Blocking Voltage		
I_{FRM}	Repetitive Peak Forward Current	300	mA
I_O	Average Forward Current	100	mA
I_{FSM}	Non-Repetitive Peak Forward Current ^{*1}	2	A
P_D	Power Dissipation	200	mW
T_J	Junction Temperature	150	°C
T_{STG}	Storage Temperature	-55 to +150	°C

*1: Pulse width = 1 μ s


Electrical Characteristics (Ta = 25 °C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
V_R	Reverse Voltage	$I_R=100\mu A$	75			V
V_F	Forward Voltage	$I_F=5mA$	0.62		0.72	V
		$I_F=10mA$			0.855	
		$I_F=100mA$			1.0	
		$I_F=150mA$			1.25	
I_R	Reverse Leakage Current	$V_R=80V$ $V_R=20V$			100 25	nA
C	Capacitance	$V_R = 0.5V, f = 1MHz$			3	pF
T_{RR}	Reverse Recovery Time	$I_F = I_R = 10mA$ $I_{RR} = 1mA, R_L = 100\Omega$			4	ns


Characteristics Curves




Forward current(I_F) vs Forward voltage(V_F)



Reverse current(I_R) vs Reverse voltage(V_R)



Power Derating Curve




Capacitance vs Reverse voltage(V_R)

ORDERING INFORMATION

Device	Package	Shipping	Tape wide	Emboss pitch	Tape specification	Notes
BAS16L	DFN1006-2L	Tape & Reel 10000pcs /7" Reel	8mm	4mm	Conductive	

Package Dimensions



NOTICE

POPPULA'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS COMPONENTS IN ANY LIFE SUPPORT DEVICES OR SYSTEMS.

POPPULA reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. POPPULA does not assume any liability arising out of the application or use of any product described herein.