









2399611-4	K/L/M	3POS.PIN DIA 14.0 HDR ASSY.90DEG	CODE HOUSING	M	PA66-GF	AQUA RED	(925)	1	12
			CODE HOUSING	L	PA66-GF	AQUA BROWN		1	11
			CODE HOUSING	K	PA66-GF	AQUA GREEN		1	10
			FOLLOW 2399611-1	-	-	-		-	1-9
2399611-3	G/H/J	3POS.PIN DIA 14.0 HDR ASSY.90DEG	CODE HOUSING	J	PA66-GF	ORANGE	(925)	1	12
			CODE HOUSING	H	PA66-GF	YELLOW		1	11
			CODE HOUSING	G	PA66-GF	RED		1	10
			FOLLOW 2399611-1	-	-	-		-	1-9
2399611-2	D/E/F	3POS.PIN DIA 14.0 HDR ASSY.90DEG	CODE HOUSING	F	PA66-GF	BROWN	(925)	1	12
			CODE HOUSING	E	PA66-GF	GREEN		1	11
			CODE HOUSING	D	PA66-GF	PURPLE		1	10
			FOLLOW 2399611-1	-	-	-		-	1-9
2399611-1	A/B/C	3POS.PIN DIA 14.0 HDR ASSY.90DEG	CODE HOUSING	C	PA66-GF	BLUE	(925)	1	12
			CODE HOUSING	B	PA66-GF	NATURE		1	11
			CODE HOUSING	A	PA66-GF	BLACK		1	10
			HEADER TPA	-	PA66-GF	RED		3	9
			FINGER PROTECTION CAP	-	PA66-GF	BLACK		3	8
			FACE SEAL	-	SILICONE	RED		1	7
			BUSBAR OVERMOLD FRONT SIDE	-	-	-		3	6
			OUTER HOUSING	-	PA66-GF	BLACK		3	5
			INNER HOUSING	-	PA66-GF	BLACK		3	4
			HV INTERLOCK CABLE BRIDGED	-	-	-		2	3
			HV INTERLOCK CABLE	-	-	-		2	2
			HEADER HOUSING 90DEG 3POS	-	AL-ALLOY	NICKEL PLATED		1	1
TE-ASSY-NO	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM




- 1. MATING CONNECTOR REFER TO DRAWING 2400957
- △ CODING VARIANT
- △ FREE SPACE FOR HEADER
- △ SEALING AREA AND BURR TOOL PARTING SHRINKAGE. CAVITIES AND GATE MARKS PERMITTED. SURFACE ROUGHNESS: Ra=1.6
- △ DRAFT ANGLE UP TO 0.5° PERMITTED
- △ MOUNTING SCREW M5. SCREW TYPE UP TO MANUFACTURER. DRILL HOLE DESIGN ACCORDING TO SCREW TYPE
- △ MATERIAL CORROSION RESISTANT. ELECTROCONDUCTIVE
- △ SCREW MB FOR BUSBAR CONNECTION
- △ ALL THREAD HOLES ARE BLIND HOLES
- △ INTERFACE PANEL CODE SEE SHEET 4



THIS DRAWING IS A CONTROLLED DOCUMENT.				DATE	29DEC2021		TE Connectivity		
DRAWN BY				S.TAN	29DEC2021				
DIMENSIONS:				REV	29DEC2021	NAME	3P05.PIN DIA 14.0.HDR ASSY.90DEG		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC			HYP-D14.00		
2-PLC ±0.5				APP. 10-16.407		SIZE	CASE CODE	DRAWING NO.	RESERVED TO
3-PLC ±0.1				APPLICATION SPEC					
4-PLC ±0.001				11-16.0222		SCALE	2:1	SHEET	1 OF 4
5-PLC ±0.001				SEE TABLE					
6-PLC ±0.001				SEE DRAWING					
7-PLC ±0.001									
8-PLC ±0.001									
9-PLC ±0.001									
10-PLC ±0.001									
11-PLC ±0.001									
12-PLC ±0.001									
13-PLC ±0.001									
14-PLC ±0.001									
15-PLC ±0.001									
16-PLC ±0.001									
17-PLC ±0.001									
18-PLC ±0.001									
19-PLC ±0.001									
20-PLC ±0.001									
21-PLC ±0.001									
22-PLC ±0.001									
23-PLC ±0.001									
24-PLC ±0.001									
25-PLC ±0.001									
26-PLC ±0.001									
27-PLC ±0.001									
28-PLC ±0.001									
29-PLC ±0.001									
30-PLC ±0.001									
31-PLC ±0.001									
32-PLC ±0.001									
33-PLC ±0.001									
34-PLC ±0.001									
35-PLC ±0.001									
36-PLC ±0.001									
37-PLC ±0.001									
38-PLC ±0.001									
39-PLC ±0.001									
40-PLC ±0.001									
41-PLC ±0.001									
42-PLC ±0.001									
43-PLC ±0.001									
44-PLC ±0.001									
45-PLC ±0.001									
46-PLC ±0.001									
47-PLC ±0.001									
48-PLC ±0.001									
49-PLC ±0.001									
50-PLC ±0.001									
51-PLC ±0.001									
52-PLC ±0.001									
53-PLC ±0.001									
54-PLC ±0.001									
55-PLC ±0.001									
56-PLC ±0.001									
57-PLC ±0.001									
58-PLC ±0.001									
59-PLC ±0.001									
60-PLC ±0.001									
61-PLC ±0.001									
62-PLC ±0.001									
63-PLC ±0.001									
64-PLC ±0.001									
65-PLC ±0.001									
66-PLC ±0.001									
67-PLC ±0.001									
68-PLC ±0.001									
69-PLC ±0.001									
70-PLC ±0.001									
71-PLC ±0.001									
72-PLC ±0.001									
73-PLC ±0.001									
74-PLC ±0.001									
75-PLC ±0.001									
76-PLC ±0.001									
77-PLC ±0.001									
78-PLC ±0.001									
79-PLC ±0.001									
80-PLC ±0.001									
81-PLC ±0.001									
82-PLC ±0.001									
83-PLC ±0.001									
84-PLC ±0.001									
85-PLC ±0.001									
86-PLC ±0.001									
87-PLC ±0.001									
88-PLC ±0.001									
89-PLC ±0.001									
90-PLC ±0.001									
91-PLC ±0.001									
92-PLC ±0.001									
93-PLC ±0.001									
94-PLC ±0.001									
95-PLC ±0.001									
96-PLC ±0.001									
97-PLC ±0.001									
98-PLC ±0.001									
99-PLC ±0.001									
100-PLC ±0.001									

REVISIONS				
P	LTN	DESCRIPTION	DATE	APPD
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

SEE TABLE

TE CONNECTIVITY
TE CONNECTIVITY
TE CONNECTIVITY

TE CONNECTIVITY
TE CONNECTIVITY
TE CONNECTIVITY

TE CONNECTIVITY
TE CONNECTIVITY
TE CONNECTIVITY

DATE: 29DEC2021
BY: S.TAN
CHK: J.L.L.
APPROV: 29DEC2021

PRODUCT SPEC: 114-160222
APPLICATION SPEC: 114-160222
WEIGHT: SEE TABLE
CUSTOMER DRAWING

NAME: 3POS.PIN DIA 14.0.HDR ASSY.90DEG HVP-HD1400

SIZE: A0
CASE CODE: 00779
DRAWING NO: C=2399611

RESTRICTED TO: -
REV: A1

SCALE: 2:1
SHEET: 3 OF 4

DATE: 29DEC2021
BY: S.TAN
CHK: J.L.L.
APPROV: 29DEC2021

4895 (3/1/3)

