


# MALE PCB PINS

## SOLDER TERMINALS PIN TYPE

### 2318

2318-X-00-XX-00-00-07-0

Swage mount in 1,57 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2318-1            | 0,79            | 1,30     |
| 2318-2            | 1,57            | 2,08     |
| 2318-3            | 2,39            | 2,87     |

### 2309

2309-X-00-XX-00-00-07-0

Swage mount in 1,63 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2309-1            | 0,79            | 1,37     |
| 2309-2            | 1,57            | 2,13     |
| 2309-3            | 2,39            | 2,92     |
| 2309-4            | 3,18            | 3,73     |

### 2514

2514-2-00-XX-00-00-07-0

Press-fit in 1,78 mounting hole



#### SPECIFICATIONS:

**Pin Material:** Brass Alloy 360, 1/2 Hard  
( Swage pins are annealed )

**Dimensions:** Millimeters

**Tolerances On:** Lengths:  $\pm 0,13$   
Diameters:  $\pm 0,051$   
Angles:  $\pm 2^\circ$



ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER (60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com