





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	REVISED PER ECO-13-010626	07AUG2013	KH	RP
			G	REVISED PER ECO-19-009248	05JUL2019	AP	SY



- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS
OF TE PRODUCT SPECIFICATION 108-2303; BASED ON
TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY
LEVEL III, APPLICATIONS IN CONTROLLED
ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE
AND STANDARD IN APPROXIMATE AREA SHOWN
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY
CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE
APPROVED LUBRICANT. TECHNICAL REFERENCE
GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- 7 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA.



○ = SIGNAL
⊗ = GROUND
RECOMMENDED PC BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. MAGARO 15JUN2007	TE Connectivity	
DIMENSIONS:		CHK W. DAVIS 15JUN2007		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. DAVIS 15JUN2007	NAME	
	0 PLC ±	PRODUCT SPEC	HEADER ASSEMBLY, RIGHT WALL, 3 PAIR, 16 COLUMN TinMan	
	1 PLC ±	APPLICATION SPEC		
	2 PLC ±		SIZE	CAGE CODE
	3 PLC ±		A1	00779
	4 PLC ±		©=1934345	
MATERIAL	FINISH	WEIGHT	Customer Drawing	RESTRICTED TO
1	2	-		-
		SCALE 8:1	SHEET 1 OF 1	REV G