







SECTION P-P

SIGN	DATE	DESCRIPTION	APPROVER
Δ	06/28'13	Add the dimensional label	Jacky
Δ	06/28'13	Add the terminal lever colour	Jacky
Δ	06/28'13	Add the colour code	Jacky
Δ	06/28'13	Change the drawing number	Jacky
Δ	06/28'13	Add the view	Jacky

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ㉑ Terminal(lever): Thermoplastic (UL94V-0)OrangeΔ
- Item ㉒ Terminal(up body): Thermoplastic (UL94V-0)
- Item ㉓ Wire guard: Stainless steel
- Item ㉔ Male contact pin: Phbz.Tin plated
- Item ㉕ Flange screw NUT: Brass M 2.5
- Item ㉖ Terminal(down body): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300 V
- Current rating: 4 A
- Wire range:
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus
- Critical dimension: Δ

H5 xx 30 x 2 xxxx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

RoHS compliant
(lead<4%)
In copper Alloy

COLOR
0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7035/D)
ΔC: GREEN (RAL 6018/U)

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

DIM		TOL			
		2P-6P	7P-12P	13P-18P	19P-24P
DimA	N×3.81+0.8	±0.10	±0.15	±0.20	±0.30
DimB	(N-1)×3.81	±0.10	±0.15	±0.20	±0.30
DimC	(N-1)×3.81+9.0	±0.15	±0.20	±0.30	±0.40
DimD	N×3.81+10.4	±0.15	±0.20	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H5 3.81mm Flange with screw NUT Series				
PART NO.	H5xx30x2xxxxG			DWG NO.	8H50202 Δ
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Jacky 2013.06.28	Jacky 2013.06.28	UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				SHEET: 01/01	X.XX ±0.10
				REV.: C	X° ±1°