



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECO-20-001327	05JUN2020	SB	JO


D




C




B



A




0.00038[.000015] GOLD IN THE CONTACT AREA,
0.00254-0.00508[.000100-.000200]
MATTE TIN-LEAD ON THE SOLDER TAIL,
ALL OVER 0.00127[.000050] NICKEL




POINT OF MEASUREMENT FOR PLATING THICKNESS



THE NOTED DIMENSIONS APPLY FROM THE BASIC
DIMENSION LINE (NOT THE POST CENTERLINE)
TO THE SURFACE INDICATED



ONE POLARIZATION SLOT FOR 2 POSITION ASSEMBLY ONLY.




DIMENSIONS NOTED ARE FOR SOLDER
STENCIL LAYOUT FOR USE WITH 1.57 ± 0.02 [.062 ± .008]
THICK PRINTED CIRCUIT BOARDS.

6


PARTS ARE PACKAGED IN GANG OF TUBES




0.00038[.000015] GOLD IN THE CONTACT AREA,
0.00254-0.00508[.000100-.000200]
MATTE TIN ON THE SOLDER TAIL,
ALL OVER 0.00127[.000050] NICKEL.




OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF



SECTION A-A



SUPERSEDED BY 6-104910-2

SUPERSEDED

7	65.91 [2.595]	64.01 [2.520]	60.96 [2.400]	24	25	7-104910-4
7	63.37 [2.495]	61.47 [2.420]	58.42 [2.300]	23	24	7-104910-3
7	60.83 [2.395]	58.93 [2.320]	55.88 [2.200]	22	23	7-104910-2
7	58.29 [2.295]	56.39 [2.220]	53.34 [2.100]	21	22	7-104910-1
7	55.75 [2.195]	53.85 [2.120]	50.80 [2.000]	20	21	7-104910-0
7	53.21 [2.095]	51.31 [2.020]	48.26 [1.900]	19	20	6-104910-9
7	50.67 [1.995]	48.77 [1.920]	45.72 [1.800]	18	19	6-104910-8
7	48.13 [1.895]	46.23 [1.820]	43.18 [1.700]	17	18	6-104910-7
7	45.59 [1.795]	43.69 [1.720]	40.64 [1.600]	16	17	6-104910-6
7	43.05 [1.695]	41.15 [1.620]	38.1 [1.500]	15	16	6-104910-5
7	40.51 [1.595]	38.61 [1.520]	35.56 [1.400]	14	15	6-104910-4
7	37.97 [1.495]	36.07 [1.420]	33.02 [1.300]	13	14	6-104910-3
7	35.43 [1.395]	33.53 [1.320]	30.48 [1.200]	12	13	6-104910-2
1	65.91 [2.595]	64.01 [2.520]	60.96 [2.400]	24	25	2-104910-4
1	63.37 [2.495]	61.47 [2.420]	58.42 [2.300]	23	24	2-104910-3
1	60.83 [2.395]	58.93 [2.320]	55.88 [2.200]	22	23	2-104910-2
1	58.29 [2.295]	56.39 [2.220]	53.34 [2.100]	21	22	2-104910-1
1	55.75 [2.195]	53.85 [2.120]	50.80 [2.000]	20	21	2-104910-0
1	53.21 [2.095]	51.31 [2.020]	48.26 [1.900]	19	20	1-104910-9
1	50.67 [1.995]	48.77 [1.920]	45.72 [1.800]	18	19	1-104910-8
1	48.13 [1.895]	46.23 [1.820]	43.18 [1.700]	17	18	1-104910-7
1	45.59 [1.795]	43.69 [1.720]	40.64 [1.600]	16	17	1-104910-6
1	43.05 [1.695]	41.15 [1.620]	38.1 [1.500]	15	16	1-104910-5
1	40.51 [1.595]	38.61 [1.520]	35.56 [1.400]	14	15	1-104910-4
1	37.97 [1.495]	36.07 [1.420]	33.02 [1.300]	13	14	1-104910-3
1	35.43 [1.395]	33.53 [1.320]	30.48 [1.200]	12	13	1-104910-2
PLATING	D	C	B	A	NO OF POSN	PART NUMBER

104910

B

A

RECOMMENDED PC BOARD MOUNTING DIMENSIONS
RECOMMENDED STENCIL THICKNESS = 0.25[.010]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. BRANDBERG 10-13-94	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK J. GESFORD 10-13-94				
		APVD D. DUPLER 10-13-94	NAME HEADER ASSY, AMPMODU MTE, VERTICAL SINGLE ROW, 2.54[.100] POLARIZED WITH LATCHING, HIGH TEMP			
		PRODUCT SPEC	SIZE A2			
		APPLICATION SPEC	CAGE CODE 00779			
MATERIAL HOUSING: HIGH TEMPERATURE LCP COLOR-BLACK POSTS: BRASS		FINISH SEE TABLE	WEIGHT -		DRAWING NO C=104910	
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV J