



文件名称	制造标准	文件编号	WI-R&D-050	生效日期	2024/12/5	版本号A0	页码	1月11日
------	------	------	------------	------	-----------	-------	----	-------

1.尺寸(单位:mm)



Series	A	B	C	D	E	I Typ	J Typ	H Typ
ZD0630	6.6±0.2	7.0±0.3	2.8±0.2	1.6±0.3	2.9±0.3	2.35	3.7	3.5
2. 产品编号	电感	DCR	饱和电流		温升电流			
	@100KHZ, 1V	Max.	Max	Typ.	Max	Typ.		
单位	μ	mΩ	A		A			
项目	L	DCR	Isat		Irms			
ZD0630-R10M	0.10±20%	1.7	53.00	60.0	28.5	32.5		
ZD0630-R22M	0.22±20%	3.0	27.20	34.0	21.0	24.0		
ZD0630-R33M	0.33±20%	3.5	20.00	25.0	19.0	21.0		
ZD0630-R47M	0.47±20%	4.1	16.00	20.0	16.5	18.0		
ZD0630-R56M	0.56±20%	4.5	14.40	18.0	15.0	16.5		
ZD0630-R68M	0.68±20%	5.3	13.60	17.0	14.5	16.0		
ZD0630-R82M	0.82±20%	6.0	12.80	16.0	12.5	14.0		
ZD0630-1R0M	1.0±20%	8.5	12.00	15.0	10.5	12.0		
ZD0630-1R5M	1.5±20%	12.1	9.60	12.0	10.5	12.0		
ZD0630-2R2M	2.2±20%	15.0	8.00	10.0	8.5	9.5		
ZD0630-3R3M	3.3±20%	26.0	7.60	9.5	7.5	8.5		
ZD0630-4R7M	4.7±20%	33.0	7.20	9.0	5.0	6.0		
ZD0630-5R6M	5.6±20%	42.0	5.20	6.5	4.8	5.5		
ZD0630-6R8M	6.8±20%	48.0	4.80	6.0	4.2	5.0		
ZD0630-8R2M	8.2±20%	60.0	4.40	5.5	4.2	5.0		
ZD0630-100M	10±20%	68.0	4.40	5.5	3.8	4.5		
ZD0630-150M	15±20%	113.0	3.20	4.0	2.3	3.0		

3.1. 包装尺寸 (单位: mm)



3.2 每卷包装数量:

规格系列	卷盘尺寸						
ZD0630	A	B		C		E	
	330±2.0	100+0.5/-0.2		13.4+0.3/-0.4		16.4+2.0/-0	
	载带尺寸						
	W	P	P0	K0	T	A0	B0
	16.0±0.3	12.0±0.1	4.0±0.1	3.3±0.1	0.35±0.0	7.0±0.1	7.5±0.1