



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		A1	REVISED PER ECO-15-006065	22APR2015	NK	RH

D


C

B


A



P.C. MOUNTING



VERTICAL LAYOUT



SPECIFICATIONS

MECHANICAL LIFE: 30,000 MAKE AND BREAK CYCLES.
CONTACT RESISTANCE: 20 mΩ MAX. INITIAL @ 2-4VDC
100mA FOR GOLD PLATED CONTACTS.
INSULATION RESISTANCE: 1,000MΩ MIN.
DIELECTRIC STRENGTH: 1,000V RMS MIN @SEA LEVEL.
OPERATING TEMPERATURE: -30°C TO 85°C.
CONTACT RATING: 0.4VA MAX @ 20V MAX (AC OR DC)

VERTICAL, SMT	PLASTIC	2-1	2-3	(ON)-ON	2	1	TBS2TBA1MZRES	2267131-6
RIGHT ANGLE, SMT	BRASS	2-1	2-3	(ON)-ON	2	1	TBS2T2A1MTRES	2267131-5
VERTICAL, SMT	PLASTIC	2-1	2-3	ON-ON	2	1	TBS1TBA1MZRES	2267131-4
RIGHT ANGLE, SMT	PLASTIC	2-1	2-3	ON-ON	2	1	TBS1TBA1MTRES	2267131-3
VERTICAL, SMT	BRASS	2-1	2-3	ON-ON	2	1	TBS1T2A1MZRES	2267131-2
RIGHT ANGLE, SMT	BRASS	2-1	2-3	ON-ON	2	1	TBS1T2A1MTRES	2267131-1
TERMINATION	ACTUATOR	POS 2	POS 1	FUNCTION	THROWS	POLES	TE DESCRIPTIVE PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.40[.015]
2 PLC ± 0.25[.010]
3 PLC ± -
4 PLC ± -
ANGLES ± 5°

FINISH

20JUN2014
DWN
NAGALAKSHMI K

20JUN2014
CHK
HILL RYAN

20JUN2014
APVD
HILL RYAN

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
SUBMINIATURE TOGGLE SWITCH,
SEALED, SMT

SIZE
A2

CAGE CODE
-

DRAWING NO
C-2267131

RESTRICTED TO
-

SCALE
1:1

SHEET
1 OF 2

REV
A1


4

3


2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
G	14			SEE SHEET 1	-	-



RIGHT ANGLE LAYOUT



P.C. MOUNTING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 20JUN2014	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL RYAN 20JUN2014				
		APVD HILL RYAN 20JUN2014	NAME			
		PRODUCT SPEC	SUBMINIATURE TOGGLE SWITCH, SEALED, SMT			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO
0 PLC ± -		—	A2		—	RESTRICTED TO
1 PLC ± 0.40[.015]		—	—		—	—
2 PLC ± 0.25[.010]		—	—		—	—
3 PLC ± -		—	—		—	—
4 PLC ± -		—	—		—	—
ANGLES ± 5°		—	—		—	—
FINISH		WEIGHT	—		—	—
MATERIAL		CUSTOMER DRAWING	SCALE		SHEET	REV
			1:1		2 OF 2	A1