



Datasheet

Gas Discharge Tubes (GDT)

Series / Models	SMD2921-200N
Product Code	10.12.10.2000
Version	A0
Date	2025-01-02
File Number	SP-GDT-246

修订历史记录

版本	日期	制/修订页次	制/修订内容	制/修订者
A0	2025-01-02	/	新发行	吴霞

Gas Discharge Tubes (GDT)

SMD2921-200N

Description


Gas discharge tubes (GDT) use noble gasses enclosed in ceramic tubes to provide an alternate circuit path for voltage spikes. The ceramic envelope and with nickel connectors allow for high loads. SMD2921 Gas Discharge Tubes (GDT) has a surge rating of 1kA, 8/20 μ s. Offered in a Squared Surface Mount package, which helps to make pick and place on PCB process easier.

This GDT series is perfectly suited for broadband equipment applications. The GDT's low off-state capacitance is compatible with high bandwidth applications and this capacitance loading value does not vary if the voltage across the GDT changes.

SMD2921 Gas Discharge Tube (GDT) is specifically designed for protection of electrical, multimedia, and communication equipment against over voltage transients in surface mount assembly applications.



Electrical symbol




Features

- I Excellent response to fast rising transients
- I Stable breakdown voltage
- I GHz working frequency
- I 8/20 μ s Impulse current capability: 1KA
- I Surface Mount package
- I Ultra Low capacitance(<0.5pF) and insertion loss
- I Size: 2.9mm*2.1mm*1.9mm

Applications

- I Communication equipment
- I CATV equipment
- I Test equipment
- I Data lines
- I Power supplies
- I Telecom SLIC protection
- I Broadband equipment
- I ADSL equipment, including ADSL2+
- I XDSL equipment
- I Satellite and CATV equipment
- I General telecom equipment

Part Number Code



Gas Discharge Tubes (GDT)

SMD2921-200N

Electrical Characteristics

DC Spark-over Voltage ^{1) 2)}	at 100V/S	200±30%	V
Impulse Spark-over Voltage	at 100V/μS	<600	V
	at 1KV/μS	<700	V
Service life			
Impulse Discharge Current	8/20μS ±5 times	1	KA
Impulse Withstanding Voltage Capacity	10/700μS, 40Ω ±5 times	6	KV
Impulse Life	10/1000μS 100 times	10	A
Insulation Resistance	at DC 100V	>1	GΩ
Capacitance	at 1MHz	<0.5	pF
Glow Voltage	at 10mA	~60	V
Arc Voltage	at 1A	~10	V
Glow to Arc transition current		<0.2	A
Weight		~0.082	g
Operation temperature		-40~+125	°C
Recommended storage ³⁾			
- Temperature		+5~+35°C	
- Humidity		45~+80%	
- Period		≤ 2 years	
Climatic category (IEC60068-1)		40/125/21	
Marking		Without	
Surface treatment		Matte-tin plated	
Moisture sensitivity level ⁴⁾		1	

¹⁾ At delivery AQL 0.65 level II, DIN ISO 2859.

²⁾ In ionized mode.

³⁾ Specified in terms of corrosion against tin plating.



⁴⁾ Tests according to JEDEC J-STD-020.

Terms in accordance with ITU-T Rec. K.12, IEC 61643-311, GB/T18802.311, GB/T 9043.

Gas Discharge Tubes (GDT)

SMD2921-200N

Dimensions(unit: mm/inch)




Recommended Soldering Pad Layout

Symbol	Millimeters	Inches
A	1.9±0.2	0.075±0.008
B	2.1±0.2	0.083±0.008
C	2.9±0.3	0.114±0.012
D	0.3±0.1	0.012±0.004
X	0.7	0.028
X1	2.9	0.114
Y	2.3	0.091

Packaging Information


Tape Specifications



Tape and reel according to IEC 60286-3

Symbol	Millimeters	Inches
W	12±0.3	0.472±0.012
A0	2.4±0.1	0.094±0.004
B0	3.2±0.1	0.126±0.004
K0	2.0±0.1	0.079±0.004
P	4.0±0.1	0.157±0.004
F	5.5±0.1	0.217±0.004
E	1.75±0.1	0.069±0.004
D	1.5+0.1/-0.0	0.059+0.004/-0.0
P0	4±0.1	0.157±0.004
P2	2±0.1	0.079±0.004
T	0.3±0.05	0.012±0.002
D0	13.3±0.15	0.524±0.006
D1	178±2	7.007±0.079
D2	60+1/-2	2.362+0.039/-0.07
W1	12.5±0.4	0.492±0.016

Reel Specifications




Packaging Quantity:

2,000 PCS per reel (7")
4 reels per inner box
8,000 PCS per inner box

Gas Discharge Tubes (GDT)

SMD2921-200N

Soldering Parameters - Reflow Soldering (Surface Mount Devices)



Reflow Condition		Pb - Free assembly
Preheat	-Temperature Min ($T_{s(min)}$)	150°C
	-Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 -180 Seconds
Average ramp up rate (Liquids Temp T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		5°C/second max
Reflow	- Temperature (T_L) (Liquids)	217°C
	- Time (min to max) (t_s)	60 -150 Seconds
Peak Temperature (T_P)		260 +0/-5°C
Time within 5°C of actual peak Temperature (t_p)		10 - 30 Seconds

Terms and definitions

NO.	Item	Definitions
1	Gas discharge tube(GDT)	A gap, or several gaps, in an enclosed discharge medium, other than air at atmospheric pressure, designed to protect apparatus or personnel, or both, from high transient voltages. Also referred to as "gas tube surge arrester".
2	DC Spark-over Voltage	The voltage at which the gas discharge tube sparks over with slowly increasing d.c. voltage.
3	Impulse Spark-over Voltage	The highest voltage which appears across the terminals of a gas discharge tube in the period between the application of an impulse of given wave-shape and the time when current begins to flow.
5	Arc voltage	Voltage drop across the GDT during arc current flow.
6	Glow voltage	Peak value of voltage drop across the GDT when a glow current is flowing.
7	Impulse discharge current 8/20μs	Current impulse with a nominal virtual front time of 8 μs and a nominal time to half-value of 20 μs.
8	Alternating Discharge Current	The rms value of an approximately sinusoidal alternating current passing through the gas discharge tube.
9	Insulation Resistance	Insulation resistance shall be measured from each terminal to every other terminal of the GDT. The test is performed with DC50V when normal spark-over Voltage 70~150V, others with DC100V.
10	Capacitance	The capacitance shall be measured once at 1 MHz between all terminals unless otherwise specified.

Cautions

- I Do not operate gas discharge tubes in power supply networks, whose maximum operating voltage exceeds the minimum spark-over voltage of the gas discharge tubes.
- I Gas discharge tubes may become hot in the event of longer periods of current stress (burn risk). In the event of overload the connectors may fail or the component may be destroyed.
- I Gas discharge tubes must be handled with care and must not be dropped.
- I Do not continue to use damaged gas discharge tubes.
- I The shown SMD pad dimensions represent a safe way to mount the arrester and are a recommendation of the manufacturer. During the reflow process it must be assured that no solder material reduces the insulation distance between the pads below the arrester.
- I SMD gas discharge tubes should be soldered within 24 month after shipment.
- I The electrical characteristics described in this datasheet are only typical characteristics, and all of these characteristics have been confirmed through testing and inspection. If the customer's usage requirements are different from this or have special requirements, please contact Ruilongyuan Electronics Co., Ltd. If protection failure or circuit damage occurs as a result, our company is not responsible for it.
- I Ruilongyuan Electronics Co., Ltd. always strives to improve our products. Consequently, the products described in this datasheet may be updated from time to time, and the corresponding product specifications may also be updated accordingly. So, before or at the time of placing your order, please check to what extent the product descriptions and specifications contained in this publication are still applicable. Ruilongyuan Electronics Co., Ltd. still reserves the right to cease production and delivery of products. Consequently, we cannot guarantee that all products listed in this datasheet will always be available. The above provisions do not apply to individual agreements with customers for specific products.
- I Ruilongyuan Electronics Co., Ltd. models may have different product codes. Different product code representations are due to the use of different production processes, but do not affect their respective product specifications.