


MALE PCB PINS

PRINTED CIRCUIT PINS

3408

3408-X-00-XX-00-00-03-0

Press-fit in 1,45 mounting hole



Basic Part
Number

Pin
Length
A


3408-1
3408-2

3,07
4,60

0270/0282

02XX-0-01-XX-00-00-03-0

Press-fit in 1,45 mounting hole



Basic Part
Number

Pin Material


0270-0
0282-0

Phosphor Bronze 544
Brass 360

0700

0700-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



8006

8006-0-00-XX-00-00-03-0


Press-fit in 0,86 mounting hole



0265

0265-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole



0275

0275-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole
Pin material is Phosphor Bronze 544 (B2)
For wire sizes up to 22 AWG



0272

0272-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole



8000

8000-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole
For wire sizes up to 22 AWG



3603

3603-0-07-XX-00-00-08-0


Annealed
Wire crimp termination. Accepts wire
sizes 20 AWG Max. / 24 AWG Min.



9976

9976-0-00-XX-00-00-03-0

Press-fit in 0,97 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except where noted)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- ◆ 80 5,08 μ m TIN OVER NICKEL (RoHS)
- ◆ 15 0,25 μ m GOLD OVER NICKEL (RoHS)
- ◆ 21 0,51 μ m GOLD OVER NICKEL (RoHS)
- ◆ 34 1,27 μ m GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com