



规格承认书

SPECIFICATION FOR APPROVAL

客户名称: Customer	深圳市立创电子商务有限公司
客户料号: CSR P/N	C46638943
产品名称: Product Name	PCB 用交流滤波电容器 AC-Filter Capacitor for PCB
型号规格: Type & Spec.	WAC-20 μ F $\pm$ 5%-300VAC
物料简码: Mat.Simple Code	AC601155
万盛料号: Walson Mat.Code	CACQ1206JE5C0155
文档编号: Document No.	SP25031902CE
发布日期: Issue Date	2025-03-19

无锡万盛电子有限公司 Wuxi Walson Electronics Co., Ltd.			客户确认 Customer Confirm
拟制 Prepared by	审核 Checked by	批准 Approval by	
张傲	陈志强	张东泽	

**无锡万盛电子有限公司**

WUXI WALSON ELECTRONICS CO., LTD.

地址 addr.: 江苏省无锡市江阴市长泾镇兴业路 22 号
No.22, Xingye RD, Changjing town, Jiangyin city, Wuxi city, Jiangsu province

电话 Tel.: 0510-88719928 传真 Fax: 0510-88716718

网址 Website: www.walson-elec.com 邮 E-mail: walson@walson-elec.com

* 本规格书归无锡万盛电子有限公司所有, 未经许可不得复制或提供给第三方; 若承认此规格书, 请签字或盖章后回传。
This specification is owned by Wuxi Walson Electronics Co., Ltd. and shall not be copied or provided to a third party without permission; If you confirmed this specification, please sign or seal it and return it to us.


版本更新记录

Version update records

版本号 Version	日 期 Date	更改说明 Change description	编制人 Prepared by	确认人 Approval by
1.0	2025-03-19	新版发行 New edition release	张 徽 Hui.Zhang	张东泽 Dongze.Zhang


■ 特点和用途 Features and applications

- ❖ 金属化聚丙烯膜，良好的电气性能，可靠性高。
Metallized polypropylene film, good electric property and high reliability.
- ❖ 阻燃塑料外壳和环氧树脂封装，镀锡铜线引出端。
Flame-retardant plastic case and epoxy resin sealing, tinned copper wire terminals.
- ❖ 适用于电源转换器的输出交流滤波电路，如 UPS、DC/AC 逆变器中的 LCL 滤波。
Suitable for output filtering for power converters, e.g. UPS, DC/AC inverter with LCL filter.
- ❖ 执行标准 Standard adopted: GB/T 17702 (idt IEC 61071)。




AC-Filter Capacitor (C3)



■ 外形尺寸 Outline dimensions



2 Pins



4 Pins



■ 技术数据 Technical Data

序 No.	项 Items		要求 Requirement			
1	额定电容量范围 Nominal capacitance range	C_N	0.33~60 μF			
2	电容量允许偏差 Permissible capacitance tolerance		$\pm 5\%$ (J), $\pm 10\%$ (K)			
3	额定均方根电压 Rated RMS voltage	U_{rms}	180 VAC	250 VAC	300 VAC	350 VAC
4	额定交流电压 Rated AC voltage	U_N	250 VAC	350 VAC	425 VAC	480 VAC
5	额定直流电压 Rated DC voltage	U_{NDC}	300 VDC	475 VDC	560 VDC	600 VDC
6	非周期冲击电压 Non-recurrent surge voltage	U_S	540 VDC	750 VDC	900 VDC	1050 VDC
7	最大工作电流 Maximum operating current	I_{max}	见技术数据表 See the technical data table			
8	最大电压脉冲斜率 Maximum voltage pulse slope	dV/dt	见技术数据表 See the technical data table			
9	最大峰值电流 Maximum peak current	$\hat{I}$	$C_N \times dV/dt$ (A)			
10	最大冲击电流 Maximum surge current	$\hat{I}_S$	$3 \times C_N \times dV/dt$ (A)			
11	损耗角正切值 Tangent of loss angle	$\tan\delta$	≤ 0.0020 (1 kHz)			
12	等效串联电阻 (典型值) Equivalent series resistance (typical value)	R_{esr}	见技术数据表 See the technical data table			
13	自感 Self inductance	L_S	$< 1 \text{ nH/mm}$ 脚距和线长 of lead pitch and length			
14	自放电时间常数 Self discharge time constant	$R_{\text{ins}} \times C$ or τ	$\geq 5000 \text{ s}$ or $\text{M}\Omega \cdot \mu\text{F}$ (20 $^{\circ}\text{C}$, 100 V, 1 min)			
15	极间耐电压 Voltage test between terminals	$U_{\text{T-T}}$	1.5 U_N or 1050 VDC 10 s, 无永久性击穿或飞弧 Neither permanent puncture nor flash-over occur			
16	极壳交流耐电压 AC voltage test between terminals&case	$U_{\text{T-C}}$	3000 VAC/50 Hz, 10 s, 无击穿或飞弧 Neither puncture nor flash-over occur			
17	额定温度 Rated temperature	θ_N	85 $^{\circ}\text{C}$			
18	运行温度范围 Operating temperature range	θ_{op}	-40 $^{\circ}\text{C}$ ~105 $^{\circ}\text{C}$ ($> 85^{\circ}\text{C}$, 每升高 1 $^{\circ}\text{C}$ 电压降额 1.5 % voltage derating 1.5% per $^{\circ}\text{C}$)			
19	贮存温度范围 Storage temperature range	θ_{stor}	-40 $^{\circ}\text{C}$ ~105 $^{\circ}\text{C}$			
20	气候类别 Climate category		40/85/56			
21	预期工作寿命 Expected service lifetime	t_{SL}	100000 h @ U_N , $\theta_{\text{hs}}=70^{\circ}\text{C}$			
22	失效率 Failure rate	λ	$< 100 \text{ Fit}$			
23	允许过电压 Permissible over voltage		1.1 U_N : 30 % of on-load duration 1.15 U_N : 30 min/day 1.2 U_N : 5 min/day 1.3 U_N : 1 min/day 1.5 U_N : 30 ms, 1000 times within lifetime			
24	最大海拔高度 Maximum altitude		3500 m ($> 1000 \text{ m}$, 每升高 500 m 电压降额 3 % voltage derating 3 % per 500 m)			

■ 技术数据表 Technical Data Table

U_{rms}=180Vac, U_N=250Vac, U_{NDC}=300Vdc											
C _N μF	W ±1 mm	H ±1 mm	T ±1 mm	P ±0.5 mm	b ±0.5 mm	d ±0.05 mm	L _s nH	dV/dt V/μs	R _{esr} 10kHz mΩ	I _{max} A	物料编码 P/N
4.0	32.0	22.0	13.0	27.5	-	1.0	16	70	8.7	7	CACL4405*H27****
5.0	32.0	28.0	14.0	27.5	-	1.0	18	70	6.9	8	CACL4505*H27****
6.8	32.0	33.0	18.0	27.5	-	1.2	21	70	5.1	11	CACL4685*E27****
10.0	32.0	33.0	18.0	27.5	-	1.2	20	70	3.5	13	CACL4106*E27****
10.0	41.5	32.0	17.0	37.5	-	1.2	22	40	6.4	10	CACL4106*E37****
15.0	42.0	40.0	20.0	37.5	-	1.2	24	40	4.3	14	CACL4156*E37****
18.0	42.0	44.0	24.0	37.5	-	1.2	25	40	3.5	14	CACL4186*E37****
20.0	42.0	44.0	24.0	37.5	-	1.2	25	40	3.3	14	CACL4206*E37****
22.0	42.0	44.0	24.0	37.5	-	1.2	26	40	2.9	14	CACL4226*E37****
25.0	42.0	44.0	24.0	37.5	-	1.2	27	40	2.6	14	CACL4256*E37****
30.0	42.0	45.0	30.0	37.5	-	1.2	28	40	2.1	14	CACL4306*E37****
33.0	42.0	45.0	30.0	37.5	-	1.2	29	40	2.0	14	CACL4336*E37****
40.0	57	43.5	30.0	52.5	20.3	1.2	26	20	3.4	20	CACL4406*E5C****
50.0	57	50.0	35.0	52.5	20.3	1.2	28	20	2.7	24	CACL4506*E5C****
60.0	57	50.0	35.0	52.5	20.3	1.2	29	20	2.2	27	CACL4606*E5C****
U_{rms}=250Vac, U_N=350Vac, U_{NDC}=475Vdc											
C _N μF	W ±1 mm	H ±1 mm	T ±1 mm	P ±0.5 mm	b ±0.5 mm	d ±0.05 mm	L _s nH	dV/dt V/μs	R _{esr} 10kHz mΩ	I _{max} A	物料编码 P/N
1.0	32.0	18.0	9.0	27.5	-	1.0	20	90	25.1	3	CACE2105*H27****
1.5	32.0	20.0	11.0	27.5	-	1.0	20	90	16.8	4	CACE2155*H27****
2.0	32.0	22.0	13.0	27.5	-	1.0	20	90	12.5	5	CACE2205*H27****
2.2	32.0	22.0	13.0	27.5	-	1.0	20	90	11.4	6	CACE2225*H27****
2.5	32.0	22.0	13.0	27.5	-	1.0	20	90	10.0	6	CACE2255*H27****
3.0	32.0	28.0	14.0	27.5	-	1.0	20	90	8.3	7	CACE2305*H27****
3.3	32.0	24.5	15.0	27.5	-	1.0	21	90	12	7	CACE2335*H27****
3.3	32.0	28.0	14.0	27.5	-	1.0	21	90	7.5	8	CACE2335*H27****
3.5	32.0	28.0	14.0	27.5	-	1.0	23	90	7.2	8	CACE2355*H27****
4.0	32.0	33.0	18.0	27.5	-	1.2	22	90	6.2	10	CACE2405*E27****
4.5	32.0	33.0	18.0	27.5	-	1.2	23	90	5.6	10	CACE2455*E27****
5.0	32.0	33.0	18.0	27.5	-	1.2	23	90	5.1	11	CACE2505*E27****
6.8	32.0	37.0	22.0	27.5	-	1.2	24	90	3.6	14	CACE2685*E27****
4.7	41.5	26.0	15.0	27.5	-	1.2	24	60	10.1	7	CACE2475*E2A****
5.0	41.5	26.0	15.0	27.5	-	1.2	26	60	9.5	8	CACE2505*E27****
6.0	41.5	32.0	17.0	27.5	-	1.2	26	60	7.9	9	CACE2605*E27****
6.5	41.5	32.0	17.0	37.5	-	1.2	26	60	7.3	10	CACE2655*E37****
6.8	42.0	40.0	20.0	37.5	-	1.2	27	60	7.0	10	CACE2685*E37****
7.5	42.0	40.0	20.0	37.5	-	1.2	27	60	6.4	11	CACE2755*E37****
8.0	42.0	40.0	20.0	37.5	-	1.2	27	60	6.0	12	CACE2805*E37****
10.0	42.0	40.0	20.0	37.5	-	1.2	28	60	4.8	13	CACE2106*E37****
12.0	42.0	40.0	20.0	37.5	-	1.2	29	60	3.9	14	CACE2126*E37****
15.0	42.0	44.0	24.0	37.5	-	1.2	30	60	3.1	14	CACE2156*E37****
18.0	42.0	45.0	30.0	37.5	-	1.2	31	60	2.6	14	CACE2186*E37****

20.0	42.0	45.0	30.0	37.5	-	1.2	32	60	2.3	14	CACE2206*E37****
22.0	42.0	45.0	30.0	37.5	-	1.2	33	60	2.2	14	CACE2226*E37****
25.0	57.5	45.0	30.0	52.5	20.3	1.2	31	30	4.3	18	CACE2256*E5C****
30.0	57.5	45.0	30.0	52.5	20.3	1.2	32	30	3.5	20	CACE2306*E5C****
35.0	57.5	50.0	35.0	52.5	20.3	1.2	32	30	3.0	23	CACE2356*E5C****
40.0	57.5	50.0	35.0	52.5	20.3	1.2	33	30	2.6	25	CACE2406*E5C****

U_{rms}=300Vac, U_N=425Vac, U_{NDC}=560Vdc

C _N μF	W ±1 mm	H ±1 mm	T ±1 mm	P ±0.5 mm	b ±0.5 mm	d ±0.05 mm	L _s nH	dV/dt V/μs	R _{esr} 10kHz mΩ	I _{max} A	物料编码 P/N
1.0	32.0	20.0	11.0	27.5	-	1.0	16	100	20.7	4	CACQ1105*H27****
1.5	32.0	22.0	13.0	27.5	-	1.0	17	100	13.8	5	CACQ1155*H27****
2.0	32.0	28.0	14.0	27.5	-	1.0	18	100	11.6	6	CACQ1205*H27****
2.2	32.0	28.0	14.0	27.5	-	1.0	18	100	10.4	7	CACQ1225*H27****
2.5	32.0	28.0	14.0	27.5	-	1.0	19	100	9.4	8	CACQ1255*H27****
3.0	32.0	33.0	18.0	27.5	-	1.2	21	100	8.3	9	CACQ1305*E27****
3.3	32.0	33.0	18.0	27.5	-	1.2	20	100	6.9	10	CACQ1335*E27****
3.5	32.0	33.0	18.0	27.5	-	1.2	21	100	6.2	10	CACQ1355*E27****
4.0	32.0	33.0	18.0	27.5	-	1.2	21	100	6.0	11	CACQ1405*E27****
4.7	32.0	37.0	22.0	27.5	-	1.2	22	100	5.2	13	CACQ1475*E27****
5.0	32.0	37.0	22.0	27.5	-	1.2	22	100	4.4	13	CACQ1505*E2A****
6.8	32.0	37.0	22.0	27.5	-	1.2	23	100	4.2	14	CACQ1685*E27****
3.0	41.5	26.0	15.0	37.5	-	1.2	22	70	13.1	6	CACQ1305*E37****
3.3	41.5	26.0	15.0	37.5	-	1.2	22	70	12.0	7	CACQ1335*E37****
3.5	41.5	32.0	17.0	37.5	-	1.2	23	70	11.2	7	CACQ1355*E37****
4.0	41.5	32.0	17.0	37.5	-	1.2	24	70	9.9	8	CACQ1405*E37****
4.5	41.5	32.0	17.0	37.5	-	1.2	24	70	8.7	9	CACQ1455*E37****
4.7	41.5	32.0	17.0	37.5	-	1.2	24	70	8.3	9	CACQ1475*Z27****
5.0	42.0	40.0	20.0	37.5	-	1.2	24	70	7.8	10	CACQ1505*E37****
6.0	42.0	40.0	20.0	37.5	-	1.2	25	70	6.5	11	CACQ1605*E37****
6.8	42.0	40.0	20.0	37.5	-	1.2	25	70	5.7	12	CACQ1685*E37****
8.0	42.0	40.0	20.0	37.5	-	1.2	26	70	4.9	13	CACQ1805*E37****
10.0	42.0	44.0	24.0	37.5	-	1.2	28	70	3.9	14	CACQ1106*E37****
12.0	42.0	45.0	30.0	37.5	-	1.2	29	70	3.3	14	CACQ1126*E37****
15.0	42.0	45.0	30.0	37.5	-	1.2	30	70	2.7	14	CACQ1156*E37****
18.0	57	43.5	30.0	52.5	20.3	1.2	29	40	4.9	17	CACQ1186*E5C****
20.0	57	43.5	30.0	52.5	20.3	1.2	29	40	5.0	18	CACQ1206*E5C****
22.0	57	43.5	30.0	52.5	20.3	1.2	30	40	4.0	20	CACQ1226*E5C****
25.0	57	50.0	35.0	52.5	20.3	1.2	31	40	3.5	21	CACQ1256*E5C****
28.0	57	50.0	35.0	52.5	20.3	1.2	32	40	3.1	23	CACQ1286*E5C****

U_{rms}=350Vac, U_N=480Vac, U_{NDC}=600Vdc

C _N μF	W ±1 mm	H ±1 mm	T ±1 mm	P ±0.5 mm	b ±0.5 mm	d ±0.05 mm	L _s nH	dV/dt V/μs	R _{esr} 10kHz mΩ	I _{max} A	物料编码 Material code
0.33	32.0	18.0	9.0	27.5	-	0.8	17	60	70.1	2	CACR2334*Z27****
0.39	32.0	18.0	9.0	27.5	-	0.8	17	60	59.8	2	CACR2394*Z27****
0.47	32.0	18.0	9.0	27.5	-	0.8	17	60	50.2	2	CACR2474*Z27****
0.68	32.0	20.0	11.0	27.5	-	0.8	18	60	35.8	3	CACR2684*Z27****
0.82	32.0	22.0	13.0	27.5	-	0.8	18	60	30.3	3	CACR2824*Z27****

1.0	32.0	22.0	13.0	27.5	-	0.8	18	60	25.5	4	CACR2105*Z27****
1.5	32.0	28.0	14.0	27.5	-	0.8	19	60	18.2	4	CACR2155*Z27****
2.0	32.0	30.0	16.0	27.5	-	0.8	21	60	14.4	5	CACR2205*Z27****
2.2	32.0	30.0	16.0	27.5	-	0.8	20	60	13.5	5	CACR2225*Z27****
2.5	32.0	33.0	18.0	27.5	-	1.0	22	60	9.1	7	CACR2255*H27****
3.0	32.0	37.0	22.0	27.5	-	1.0	24	60	9.6	7	CACR2305*H27****
3.3	32.0	37.0	22.0	27.5	-	1.0	24	60	6.9	8	CACR2335*H27****
3.5	32.0	37.0	22.0	27.5	-	1.0	23	60	6.5	8	CACR2355*H27****
4.0	32.0	37.0	22.0	27.5	-	1.0	23	60	5.7	8	CACR2405*H27****
4.0	31.0	37.0	22.0	27.5	-	1.0	23	50	7.5	8.5	CACR2405*H271***
1.5	41.5	26.0	15.0	37.5	-	1.0	25	40	25.1	9	CACR2155*H37****
2.0	41.5	26.0	15.0	37.5	-	1.0	26	40	19.4	3	CACR2205*H37****
2.2	41.5	26.0	15.0	37.5	-	1.0	25	40	17.8	4	CACR2225*H37****
2.5	41.5	32.0	17.0	37.5	-	1.0	27	40	16.0	5	CACR2255*H37****
3.0	41.5	32.0	17.0	37.5	-	1.0	26	40	13.7	5	CACR2305*H37****
3.3	41.5	32.0	17.0	37.5	-	1.0	29	40	12.6	6	CACR2335*H37****
3.5	41.5	32.0	17.0	37.5	-	1.0	28	40	12.1	6	CACR2355*H37****
4.0	42.0	40.0	20.0	37.5	-	1.0	29	40	10.8	7	CACR2405*H37****
4.5	42.0	40.0	20.0	37.5	-	1.0	31	40	9.9	7	CACR2455*H37****
5.0	42.0	40.0	20.0	37.5	-	1.0	30	40	9.1	7	CACR2505*H37****
5.5	42.0	40.0	20.0	37.5	-	1.0	29	40	8.6	8	CACR2555*H37****
6.0	42.0	44.0	24.0	37.5	-	1.0	32	40	8.1	9	CACR2605*H37****
6.5	42.0	44.0	24.0	37.5	-	1.0	31	40	7.5	9	CACR2655*H37****
7.0	42.0	44.0	24.0	37.5	-	1.0	31	40	7.2	10	CACR2455*H37****
7.5	42.0	44.0	24.0	37.5	-	1.0	30	40	6.9	10	CACR2505*H37****
8.0	42.0	44.0	24.0	37.5	-	1.0	30	40	6.6	11	CACR2305*H37****
8.5	42.0	45.0	30.0	37.5	-	1.0	32	40	6.4	11	CACR2355*H37****
9.0	42.0	45.0	30.0	37.5	-	1.0	31	40	6.1	11	CACR2855*H37****
9.5	42.0	45.0	30.0	37.5	-	1.0	33	40	5.9	11	CACR2955*H37****
10.0	42.0	45.0	30.0	37.5	-	1.0	32	40	5.7	11	CACR2106*H37****
10.0	57.0	43.5	30.0	52.5	-	1.2	34	30	7.4	12	CACR2106*E5C****
11.0	57.0	43.5	30.0	52.5	-	1.2	33	30	6.9	12	CACR2116*E5C****
12.0	57.0	43.5	30.0	52.5	20.3	1.2	29	30	5.7	14	CACR2126*E5C****
15.0	57.0	50.0	35.0	52.5	20.3	1.2	31	30	4.8	17	CACR2156*E5C****
16.0	57.0	50.0	35.0	52.5	20.3	1.2	30	30	4.6	17	CACR2166*E5C****
18.0	57.0	50.0	35.0	52.5	20.3	1.2	33	30	4.2	18	CACR2186*E5C****
20.0	57.0	50.0	35.0	52.5	20.3	1.2	32	30	3.8	20	CACR2206*E5C****
22.5	57.0	55.0	38.0	52.5	20.3	1.2	33	27	4.5	21	CACR2226JE5C****

注 Notes: 其他规格尺寸等可按用户要求定制。Other specifications and sizes can be customized according to user requirements.

■ 出厂检验 OQC

序号 No.	检验项目 Check Item	抽样数 Sampling quantity			判定准则 Judge criteria	
		n≤1000	1000<n≤10000	n> 10000	Ac	Re
1	外观检查 External inspection	21	35	46	0	1
2	尺寸检测 Dimensions measurement	29	42	60	0	1
3	极间耐电压试验 Voltage test between terminals	48	73	108	0	1
4	绝缘电阻测试 Insulation resistance test				0	1
5	电容量测量 Capacitance measurement				0	1
6	损耗角正切测量 tanδ measurement				0	1
7	等效串联电阻测量 R _{esr} measurement				0	1

注 Note:

1. n 为批次数 “n” for batch quantity.

2. 若批次数超过抽样数， 全数检验 If the batch quantity exceeds the sampling quantity, conduct a full inspection.

■ 物料编码示例 Material P/N example


位序 No.	第 1 位 1st	第 2~3 位 2nd~3rd	第 4~5 位 4th~5th	第 6~8 位 6th~8th	第 9 位 9th	第 10 位 10th	第 11~12 位 11th~12th	第 13~14 位 13th~14th	第 15~16 位 15th~16th
代码 Code	C	AC	Q1	206	J	E	5C	01	55
内容 Content	产品类别 Category	产品型号 Type	额定电压 U _{rms}	标称容量 C _N	容量偏差 ΔC/C	引线规格 Lead type	引线间距 Lead space (P/b)	内部代码 Internal code	引线长度 Lead length (L)
说明 Explain	C: 电容 Capacitor	AC: WAC	L4: 180VAC E2: 250VAC Q1: 300VAC Q3: 310VAC R2: 350VAC R3: 380VAC G2: 400VAC S2: 450VAC H2: 500VAC U1: 600VAC	三位数法,即: 3 digits method I.e.: ab*10 ^c pF 例如: e.g.: 505=50*10 ⁵ pF=5 μF 406=40*10 ⁶ pF=40 μF	J: ±5 % K: ±10 %	Z: 0.8CU H: 1.0CU E: 1.2CU	22: 22.5 27: 27.5 37: 37.5 52: 52.5 2A: 27.5/10.2 2B: 27.5/12.7 3A: 37.5/10.2 3B: 37.5/12.7 3C: 37.5/20.3 5C: 52.5/20.3	内部设计代码 Internal design code	数字或数字和字母组合, 如: Number or combination of number and letter E.g.: 50=5.0 A5=15 2A=12.5 00=15min

■ 可靠性测试 Reliability test

序号 No.	测试项目 Test Item	测试方法 Test method	要求 Requirement
1	外部检查 Outline check	目视检查, 卡尺测量 Visual inspection and caliper measurement	外形规整, 无可见损伤; 标志端正、清晰、无误。The appearance is regular without visible damage; The mark is regular, clear and correct.
	初始测量 Initial measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 $\tan\delta_0$: 10 kHz, 20 °C	
	引出端强度 Robustness of terminations	(1) 拉力试验 Ua1 Tensile test Ua1 $d \leq 0.8 \text{ mm}$: 10 N $0.8 \text{ mm} < d \leq 1.2 \text{ mm}$: 20 N (2) 弯曲试验 Ub1 Bending test Ub1 $d \leq 0.8 \text{ mm}$: 5N $0.8 \text{ mm} < d \leq 1.2 \text{ mm}$: 10N 90 °反复弯曲 2 次, 持续时间 2~3 s 90 °repeated bending twice, lasting for 2 to 3 s	外观无可见损伤 No visible damage
	耐焊接热 Resistance to soldering heat	槽焊法 Tb 方法 1A Solder bath test Tb, method 1A 焊槽温度 Solder bath temp.: $260 \pm 5 \text{ }^\circ\text{C}$ 浸渍时间 Dip time: $10 \pm 1 \text{ s}$	外观无可见损伤 No visible damage
	最后测量 Final measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 $\tan\delta$: 10 kHz, 20 °C	$ \Delta C/C \leq 0.5 \%$ $\Delta \tan\delta \leq 0.005$
2	初始测量 Initial measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 $\tan\delta_0$: 10 kHz, 20 °C	
	振动 Vibration	频率 Frequency: 10~55 Hz 振幅 Amplitude: 0.35 mm 扫频循环次数 Sweep cycle times: 10 试验程序: 取三个互相垂直的方向, 每个方向持续时间为 10 个频率周期, 每分钟 1 倍频程 Test procedure: take three mutually perpendicular directions, each direction lasts for 10 frequency cycles, with 1 octave per minute	外观无可见损伤 No visible damage
	最后测量 Final measurement	极壳间耐电压试验 U_{T-C} : 无击穿或飞弧 Neither puncture nor flash-over occur 电容量 C: 1 kHz, 20 °C 损耗角正切 $\tan\delta$: 10 kHz, 20 °C	$ \Delta C/C \leq 0.5 \%$ $\Delta \tan\delta \leq 0.005$
3	初始测量 Initial measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 $\tan\delta_0$: 10 kHz, 20 °C	
	冲击放电 Surge discharge test	$\hat{I}_1 = 1.1\hat{I}_S$, 若未给出 $\hat{I}_S$ 则 $2U_{rms}$ 或 $1.1U_{NDC}$ 充电后短路放电, 5 次 $\hat{I}_1 = 1.1\hat{I}_S$, If $\hat{I}_S$ is not given, short circuit discharge after charged with $2U_{rms}$ or $1.1U_{NDC}$, 5 times	无永久性击穿或闪络 Neither permanent puncture nor flash-over occur
	最后测量 Final measurement	极间耐电压试验 U_{T-T} : $1.5U_N$ or U_S , 10 s 电容量 C: 1 kHz, 20 °C 损耗角正切 $\tan\delta$: 10 kHz, 20 °C	无永久性击穿或飞弧 Neither permanent puncture nor flash-over occur $ \Delta C/C \leq 1.0 \%$ $\Delta \tan\delta \leq 0.2 \times \tan\delta_0 + 0.001$
4	初始测量 Initial measurement	电容量: 1 kHz, 20 °C 损耗角正切 $\tan\delta_0$: 10 kHz, 20 °C	
	自愈性 Self-healing test	承受 $1.1U_S$ 和 $1.5U_{NDC}$ 二者较高电压 10 s, 若试验期间发生自愈性击穿少于 5 次, 则缓慢升高电压直至发生 5 次自愈性击穿或电压达到 $2.5U_{NDC}$ 且最多保持 10 s	外观无可见损伤 No visible damage

		Withstand the higher voltage of 1.1U _s and 1.5U _{NDC} for 10 s. If the self-healing breakdown occurs less than 5 times during the test, slowly increase the voltage until the self-healing breakdown occurs 5 times or the voltage reaches 2.5U _{NDC} and remains for 10 s at most	
	最后测量 Final measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ: 10 kHz, 20 °C	$ \Delta C/C \leq 0.5\%$ $\Delta \tan \delta \leq 0.1 \times \tan \delta_0 + 0.001$
5	初始测量 Initial measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ: 10 kHz 20 °C	
	温度快速变化 Fast temperature change	T _A =-40 °C, T _B =105 °C 5 次循环, 持续时间 t=30 min 5 cycles, duration t=30 min	外观无可见损伤 No visible damage
	最后测量 Final measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ: 10 kHz, 20 °C	$ \Delta C/C \leq 2.0\%$ $\Delta \tan \delta \leq 0.015$
6	初始测量 Initial measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ ₀ : 10 kHz, 20 °C	
	恒定湿热 Damp heat, steady state	温度 Temperature: 40±2 °C 湿度 Humidity: 93±3 %RH 持续时间 Duration: 56 days	外观无可见损伤 No visible damage
	最后测量 Final measurement	极间耐电压 U _{T-T} : 1.5U _N or U _S , 10 s 极壳耐电压 U _{T-C} : 3000 VAC, 10 s 电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ: 10 kHz, 20 °C	极间耐电压: 无永久性击穿或闪络 U _{T-T} : Neither permanent puncture nor flash-over occur 极壳耐电压: 无击穿或闪络 U _{T-C} : Neither puncture nor flash-over occur $ \Delta C/C \leq 2.0\%$, $\Delta \tan \delta \leq 0.015$
7	初始测量 Initial measurement	电容量 C: 1 kHz 20 °C 损耗角正切 Tanδ ₀ : 10 kHz 20 °C	
	热稳定性 Thermal stability test	试验温度 Test temperature: 70±2 °C 试验电流 Test current: I _{max} 测试频率 Test frequency: 10 kHz 持续时间 Duration: 48 h 中间每 2 h 测量一次电容器表面热点温度 Intermediate measure the temperature of capacitor surface hot-spot every 2 h	6 h 期间测得电容器表面热点温升变化 $\Delta^2 T \leq 1$ K The temperature rise change measured during 6 h on capacitor surface hot-spot $\Delta^2 T \leq 1$ K 表面温升 Surface temperature rise $\Delta T \leq 15$ °C
	最后测量 Final measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ: 10 kHz, 20 °C	$ \Delta C/C \leq 1.0\%$ $\Delta \tan \delta \leq 0.2 \times \tan \delta_0 + 0.0015$
8	初始测量 Initial measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ ₀ : 10 kHz, 20 °C	
	耐久性 Endurance test	试验电压 Test voltage: 1.25U _{rms} 烘箱温度 Oven temperature: 85±2 °C 试验时间 Test time: 500 h+500 h 中间充放电: 1.4Ĉ, 1000 次 Intermediate charge and discharge: 1.4Ĉ, 1000 times	外观无可见损伤 No visible damage
	最后测量 Final measurement	电容量 C: 1 kHz, 20 °C 损耗角正切 Tanδ: 10 kHz, 20 °C	$ \Delta C/C \leq 3.0\%$ $\Delta \tan \delta \leq 0.015$


■ 温度特性曲线 Temperature characteristic curve



环境温度 Ambient temperature θ_{amb} (°C)

最大工作电流与环境温度关系曲线图

Maximum working current I_W VS ambient temperature θ_{amb}



电容量变化率与温度关系曲线图

Capacitance change rate VS capacitor temperature θ_c

注: I_{max} 是 $f=10\text{ kHz}$ $\theta_{amb}=70^\circ\text{C}$ $\Delta\theta_{case}=15^\circ\text{C}$ 时最大电流有效值。温度过高将加速电容器介质的电化学老化。对于该型号电容器, 实际运行中, 电容器的内部热点温度最高不应超过 105°C 。


Note: I_{max} is the maximum RMS current when $f=10\text{ kHz}$ $\theta_{amb}=70^\circ\text{C}$ and $\Delta\theta_{case}=15^\circ\text{C}$. Too high temperature will accelerates electrochemical degradation of the dielectric.

For this type of capacitor, the maximum internal hot spot temperature shall not exceed 105°C in actual operation.

注: 电容器温度 θ_c 是指电容器的介质温度(电容器在不通电状态下在恒定环境温度中放置足够长的时间, 则可认为电容器的介质温度与环境温度相同)。


Note: θ_c is the dielectric temperature of the capacitor (It may be assumed that the dielectric temperature is the same as the ambient temperature, provided that the capacitor has been left in an nu-energized state at constant ambient temperature of an adequate period.)

■ 预期寿命曲线 Lifetime expectancy curve



■ 产品标志 Mark

标志内容 Mark	说明 description
WALSON	万盛商标 Walson logo
WAC	产品型号 Product type
20 μ F	标称容量 Nominal capacitance
$\pm 5\%$	容量偏差 Capacitance tolerance
300 VAC	额定均方根电压 Rated RMS voltage
40/85/56	气候类别 Climate category
SH	自愈性 Self-healing property
www.walson-elec.com	公司网址 Corporation website



■ 注意事项 Cautions

1. 包装好的电容器允许以任何方式运输，但应避免雨雪淋袭、腐蚀、挤压跌落损伤等。

Packaged capacitors are allowed to be transported in any way, but shall be protected from rain and snow, corrosion, crushing and falling damage, etc.

2. 电容器应保存在环境温度-10℃~40℃，相对湿度≤85%的室内，避免阳光直射、温度剧烈变化、凝露和有腐蚀性气体等。

Capacitors shall be stored indoors with ambient temperature -10℃ to 40℃ and relative humidity ≤85%, avoid direct sunlight, sharp temperature changes, condensation and corrosive gases.

3. 存贮时间超过半年的电容器，应检查确认常规电气性能和可焊性合格后方可投入使用。

Capacitors that have been stored for more than half a year shall be checked and confirmed to be qualified in conventional electrical performance and solderability before being put into use.

4. 拿取和安装过程中，应做好防护，避免引线扎伤；另应避免多次挤压、弯曲电容器引线。

In the process of taking and installing, protection shall be provided to prevent the lead from being punctured; In addition, avoid repeatedly squeezing and bending capacitor leads.

5. 焊接电容器引线时，应避免长时间过热以免影响到电容器性能。如禁止与 SMD 产品一起做回流焊接；电烙铁焊接时烙铁尖端温度应不超过 400℃，焊接时间 3 s 以内。

When welding capacitor leads, avoid overheating for a long time to avoid affecting capacitor performance. For example, reflow welding with SMD products is prohibited. The tip temperature of electric soldering iron shall not exceed 400℃, and the welding time shall be within 3 s.

6. 这类电容器的电气连接方式如下图所示：

The electrical connection method of this type of capacitor is shown in the following figure:



7. 该款电容器不得用于其他不适宜的应用场合，如谐振、吸收、接地抗干扰等；设计电路时，电容器勿贴近其他发热源（如功率管、变压器等），以免引起电容器温度过高。

This capacitor shall not be used in other unsuitable applications, such as resonance, absorption, ground EMI suppression, etc; When designing the circuit, the capacitor shall not be close to other heat sources (such as power tube, transformer, etc.), so as not to cause excessive temperature of the capacitor.

8. 电容器不得过载使用，如超过规定值的电压、电流、温度等。

Capacitors shall not be used with overload, such as voltage, current, temperature, etc. exceeding the specified value.
