




| SIGN                                           | DATE       | DESCRIPTION                                       | APPROVER |
|------------------------------------------------|------------|---------------------------------------------------|----------|
| △                                              | 2011.02.25 | The wire is changed from 14-30(AWG) to 14-28(AWG) | Aaron    |
| △                                              | 2011.02.25 | Add is cULus                                      | Aaron    |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |            |                                                   |          |



Material:

- Item a Clamp: Brass Ni plated
- Item b Male contact pin: Brass, Tin plated.
- Item c Terminal screw: Steel Zinc plating
- Item d Terminal housing: Thermoplastic (UL94V-0)
- Item e Terminal cover: Thermoplastic (UL94V-0)
- Item f Terminal(track): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 8A

- Wire range:

- △ ● Solid wire(AWG):14~28
- △ ● Stranded wire(AWG):14~28
- Torque(Lb-In):2.17
- Screw:M2
- Wire strip length: 6 mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40

 ● Safety Approval: 

V5 xx 31 x 2 xxxx G

— G: Pb<40000ppm

|              |             |
|--------------|-------------|
| No. OF POLES | —           |
| 03           | 3 CONTACTS  |
| 04           | 4 CONTACTS  |
| ...          | ...         |
| 24           | 24 CONTACTS |

Color

- 0 Black (RAL9005)  
2 Red (RAL3001/D)  
3 Orange(RAL2011/P)  
4 Yellow(RAL1018/A)  
5 Green(RAL6018/T)  
6 Blue (RAL5015/A)  
8 Grey(RAL7035/D)

0000: "@" Logo (Standard)  
000A: "ANYTEK" Mark  
Any special item by  
customer request.  
please contact sales  
department.

|      |       |                                                                                     |       |       |       |       |       |       |       |       |       |       |
|------|-------|-------------------------------------------------------------------------------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| POLE |       | 2                                                                                   | 3     | 4     | 5     | 6     | 7     | 8     | 9     | 10    | 11    | 12    |
| A    |       |  | 12.82 | 16.63 | 20.44 | 24.25 | 28.06 | 31.87 | 35.68 | 39.49 | 43.30 | 47.11 |
| B    |       |  | 7.62  | 11.43 | 15.24 | 19.05 | 22.86 | 26.67 | 30.48 | 34.29 | 38.10 | 41.91 |
| Tol. | ±0.10 |                                                                                     |       |       |       |       | ±0.15 |       |       |       |       |       |
| POLE | 13    | 14                                                                                  | 15    | 16    | 17    | 18    | 19    | 20    | 21    | 22    | 23    | 24    |
| A    | 50.92 | 54.73                                                                               | 58.54 | 62.35 | 66.16 | 69.97 | 73.78 | 77.59 | 81.40 | 85.21 | 89.02 | 92.83 |
| B    | 45.72 | 49.53                                                                               | 53.34 | 57.15 | 60.96 | 64.77 | 68.58 | 72.39 | 76.20 | 80.01 | 83.82 | 87.63 |
| Tol. | ±0.20 |                                                                                     |       |       |       |       | ±0.30 |       |       |       |       |       |

# ANYTEK

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                                                    |                     |                     |                                                                                       |             |            |           |
|----------|----------------------------------------------------|---------------------|---------------------|---------------------------------------------------------------------------------------|-------------|------------|-----------|
| TITLE    | V5 3.81 mm W/O Flange Dinrail holder A type Series |                     |                     |                                                                                       |             |            |           |
| PART NO. | V5xx31x2xxxxG                                      |                     |                     | DWG NO.                                                                               | 8V50102     |            |           |
| APPROVED | CHECKED                                            | DESIGNED            | DRAWN               | CUST NO.                                                                              |             |            | Tolerance |
|          |                                                    | Aaron<br>2011.02.25 | Jacke<br>2009.08.27 |  | UNIT: mm    | X. ±0.50   |           |
|          |                                                    |                     |                     |                                                                                       | SCALE: NONE | X.X ±0.30  |           |
|          |                                                    |                     |                     | SHEET: 01/01                                                                          | REV: C      | X.XX ±0.10 |           |
|          |                                                    |                     |                     |                                                                                       |             | X° ±1°     |           |