

承認書

SPECIFICATION FOR APPROVAL

CUSTOMER: 2144


DESCRIPTION: WIRE WOUND CHIP INDUCTOR

DDY PART NO: WI0603LD-TIA系列

CUSTOMER MODEL NO:

DRAWING		
MADE	CHECKED	APPROVED
谭晶晶	黄志伟	肖中华
DATE:	2025年2月26日	

CUSTOMER APPROVE



惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD

廣東省博羅縣洲際工業園梅園三路

NO.3 MEI YUAN ROAD,ZHOU JI INDUSTRIAL AREA,BOLUO COUNTY GUANGDONG

電話: 15970768093 13640935893

傳真: 0752-6207969

郵編: 516100

Http://ddycoils.com



惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A
DESCRIPTION:	WIRE WOUND CHIP INDUCTOR	PAGE NO:	PAGE 1 OF 7
PART NO:	WI0603LD-TIA系列	SN.	
CUSTOMER NO:		DATE:	2025年2月26日

CATALOG

Resume	P2
Shape & Dimension	P3
Part numbering ststem	P3
General specification	P3
Electrical Characteristics List	P4
Soldering Conditions	P5
Package Specifications	P6
Package Information	P7

注意：

此物料不涉及汽车或相关产品方面的应用，否则，由此引起的一切品质和责任问题，我司将概不承担。

HUI ZHOU DE LI ELECTRONICS CO., LTD

[illegible]





惠州市德立电子有限公司

HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A
DESCRIPTION:	WIRE WOUND CHIP INDUCTOR	PAGE NO:	PAGE 3 OF 7
PART NO:	WI0603LD-TIA系列	SN.	
CUSTOMER NO:		DATE:	2025年2月26日

1.SHAPE & DIMENSION



CODE		L(MAX)	W(MAX)	T(MAX)	E(Typ.)	F(Typ.)	D(Typ.)
DIMENSION	WI0603LD-TIA	1.80	1.25	1.20	0.64	1.02	0.64

2. PART NUMBERING SYSTEM

WI □□□□ □□ □R□ □ □ □ — □□
1 2 3 4 5 6 7 8

- 1 PRODUCT SYMBOL (产品代号)
- 2 DIMENSIONS (规格尺寸)
- 3 MATERIAL (芯片类型)
- 4 INDUCTANCE (电感量)
- 5 TOLERANCE (公差) : M±20%
- 6 TERMINAL (端电极材料) : S-锡端头
- 7 PACKAGING (包装方式) : T-编带盘装; B-散装
- 8 E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

3.GENERAL SPECIFICATION

- a. Rating DC current: Temperature rise(T) is 40°C approximately at Irms.
- b.Operating temp.: -40°C~ +85°C(Including self-generated heat).
- c.Storage temp.: -10°C ~ +40°C R.H.: 60% Max
- d.Moisture sensitivity level (MSL) 1
- e.Recommended products should be used within 12 months from the date of delivery

APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶

APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶




惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A
DESCRIPTION:	WIRE WOUND CHIP INDUCTOR	PAGE NO:	PAGE 5 OF 7
PART NO:	WI0603LD-TIA系列	SN.	
CUSTOMER NO:		DATE:	2025年2月26日

5. SOLDERING CONDITIONS


**Figure 1.
Re-flow
Soldering
(Lead Free)**



Note:

- Preheat circuit and products to 150°C
- 260°C tip temperature (max)
- Reflow times: no more than 2 times
- Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

**Figure 2.
Hand
Soldering**



Note:

- Use a 20 watt soldering iron with tip diameter of 1.0mm
- Limit soldering time to 3 sec.

APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶




惠州市德立电子有限公司

HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A
DESCRIPTION:	WIRE WOUND CHIP INDUCTOR	PAGE NO:	PAGE 6 OF 7
PART NO:	WI0603LD-TIA系列	SN.	
CUSTOMER NO		DATE:	2025年2月26日

6.Package Specifications

■Inside Box And Outside Carton



卷轴数量	内盒包装数量	外箱包装数量
每卷:4000 PCS	每盒四盘, 共16000 PCS	小箱6盒, 共96000 PCS
		中箱8盒, 共128000 PCS
		大箱10盒, 共160000 PCS
	内盒包装尺寸	外箱包装尺寸
	20.3*19.3*5.5cm	小号外箱, 40.6*23*19.7cm
		中号外箱, 41*22*26cm
		大号外箱, 41*22*33cm


APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶




惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A
DESCRIPTION:	WIRE WOUND CHIP INDUCTOR	PAGE NO:	PAGE 7 OF 7
PART NO:	WI0603LD-TIA系列	SN.	
CUSTOMER NO:		DATE:	2025年2月26日


7. PACKAGING(unit: mm)



胶带 POLYSTYRENE TAPE



Peeling off force
Pull strength
0402~1210:20g~80g
Speed of peeling off:
300mm/min±10%



	A	B	T
	Typ	Typ	Typ
胶带	1.15	1.83	0.95

ΦA	ΦB	ΦC	ΦD	E	W	t	
Typ	Typ	Typ	Typ	Typ	Typ	Typ	
178	60	13	21	2	8.4	2	

包装数量(PACKAGING QUANTITY): 4000Pcs/盘

APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶