

## MPO5022-331KT

### Wire Wound SMD Power Inductors

#### FEATURES

- High energy storage capacity and low DCR.
- Ferrite bobbin core and low profile, small size.
- High heat resistance, ideal for re-flow soldering.
- Operate temperature range ....  $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$  (Including self temp. rise)
- RoHS compliant

#### APPLICATIONS

- Power supply choke for small electrical equipments such as DVC, LCD display, notebook, communication equipment, OA equipment and so on.


#### Explanation of Part Number

MPO 5022 -331 K T

1 2 3 4 5

- ◆ 1:Product Series:Wire Wound SMD Power Inductor
- ◆ 2:Dimensions:
- ◆ 3: Inductance value: 331=330uH
- ◆ 4: Tolerance of Inductance:K $\pm 100\%$ ,M: $\pm 20\%$
- ◆ 5:Packing:Tape Carrier Package

#### Dimensions: [mm]



|    |         |     |
|----|---------|-----|
| A: | 18.45mm | Max |
| B: | 15.24mm | Max |
| C: | 7.11mm  | Max |
| D: | 12.7mm  | Ref |
| E: | 2.5mm   | Ref |
| F: | 2.5mm   | Ref |
| G: | 13.0mm  | Ref |


## Electrical Properties:

| MetalLions PT/NO. | Inductance<br>L( $\mu$ H) | Test Frequency | Resistance<br>RDC(m $\Omega$ ) Max. | Isat (A)Max | Marking |
|-------------------|---------------------------|----------------|-------------------------------------|-------------|---------|
| MPO5022-331KT     | 330 $\pm$ 10%             | 100kHz/0.25V   | 630                                 | 1.9         | 331     |


※Isat : Based on inductance change ( $\Delta$ L/Lo : drop 10% Max.)

## Reliability and Test Condition

### MECHANICAL

| TEST ITEM         | SPECIFICATION                                                                                | TEST DETAILS                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|-------------------|----------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Substrate bending | $\Delta L/L_0 \leq \pm 5\%$<br><br>There shall be no mechanical damage or electrical damage. | <p>The sample shall be soldered onto the printed circuit board in figure 1 and a load applied until the figure in the arrow direction is made approximately 3mm.(keep time 30 seconds)</p> <p>PCB dimension shall the page 7/9</p> <p>F(Pressurization)</p>  <p>PRESSURE ROD<br/>figure-1</p>                                                                                              |
| Vibration         | $\Delta L/L_0 \leq \pm 5\%$<br><br>There shall be no mechanical damage.                      | <p>The sample shall be soldered onto the printed circuit board and when a vibration having an amplitude of 1.52mm and a frequency of from 10 to 55Hz/1 minute repeated should be applied to the 3 directions (X,Y,Z) for 2 hours each. (A total of 6 hours)</p>                                                                                                                                                                                                              |
| Solderability     | New solder<br>More than 90%                                                                  | <p>Flux (rosin, isopropyl alcohol{JIS-K-1522}) shall be coated over the whole of the sample before hard, the sample shall then be preheated for about 2 minutes in a temperature of 130~150℃ and after it has been immersed to a depth 0.5mm below for 3±0.2 seconds fully in molten solder M705 with a temperature of 245±5℃.</p> <p>More than 90% of the electrode sections shall be covered with new solder smoothly when the sample is taken out of the solder bath.</p> |

## MECHANICAL

| TEST ITEM                                       | SPECIFICATION                         |                                                                                                                                                                                                                                                                                                                                                                                              |
|-------------------------------------------------|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Resistance to Soldering heat (reflow soldering) | There shall be no damage or problems. | <p><b>Temperature profile of reflow soldering</b></p>  <p>The specimen shall be passed through the reflow oven with the condition shown in the above profile for 1 time.</p> <p>The specimen shall be stored at standard atmospheric conditions for 1 hour, after which the measurement shall be made.</p> |


## ELECTRICAL

| TEST ITEM                    | SPECIFICATION                                                                          | TEST DETAILS                                                                                                                                                                                                                                                                                                           |
|------------------------------|----------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Insulation resistance        | There shall be no other damage or problems.                                            | <p>DC 100V voltage shall be applied across this sample of top surface and the terminal.</p> <p>The insulation resistance shall be more than <math>1 \times 10^8 \Omega</math>.</p>                                                                                                                                     |
| Dielectric withstand voltage | There shall be no other damage or problems.                                            | <p>AC 100V voltage shall be applied for 1 minute across the top surface and the terminal of this sample</p>                                                                                                                                                                                                            |
| Temperature characteristics  | $\Delta L/L20^\circ\text{C} \leq \pm 10\%$<br>$0 \sim 2000 \text{ ppm}/^\circ\text{C}$ | <p>The test shall be performed after the sample has stabilized in an ambient temperature of <math>-20</math> to <math>+85^\circ\text{C}</math>, and the value calculated based on the value applicable in a normal temperature and normal humidity shall be <math>\Delta L/L20^\circ\text{C} \leq \pm 10\%</math>.</p> |

## ENVIROMENT CHARACTERISTICS


| TEST ITEM                                                                                                  | SPECIFICATION                                                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
|------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------|----------|---|------------------------------------------------|---------|---|----------------------|-----------|---|-----------------------------------------------|---------|---|----------------------|-----------|
| High temperature storage                                                                                   | $\Delta L/L_o \leq \pm 5\%$<br><br>There shall be no mechanical damage.       | The sample shall be left for $96 \pm 4$ hours in an atmosphere with a temperature of $85 \pm 2^\circ\text{C}$ and a normal humidity.<br><br>Upon completion of the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.                                                                                                                                                                                                                                                                                                                                                                                                  |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| Low temperature storage                                                                                    | $\Delta L/L_o \leq \pm 5\%$<br><br>There shall be no mechanical damage.       | The sample shall be left for $96 \pm 4$ hours in an atmosphere with a temperature of $-25 \pm 3^\circ\text{C}$ .<br><br>Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.                                                                                                                                                                                                                                                                                                                                                                                                            |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| Change of temperature                                                                                      | $\Delta L/L_o \leq \pm 5\%$<br><br>There shall be no other damage of problems | The sample shall be subject to 5 continuous cycles, such as shown in the table 2 below and then it shall be subjected to standard atmospheric conditions for 1 hour, after which measurement shall be made. <div> <table> <caption>table 2</caption> <tr> <th></th><th>Temperature</th><th>Duration</th></tr> <tr> <td>1</td><td><math>-25 \pm 3^\circ\text{C}</math><br/>(Thermostat No.1)</td><td>30 min.</td></tr> <tr> <td>2</td><td>Standard atmospheric</td><td>No.1→No.2</td></tr> <tr> <td>3</td><td><math>85 \pm 2^\circ\text{C}</math><br/>(Thermostat No.2)</td><td>30 min.</td></tr> <tr> <td>4</td><td>Standard atmospheric</td><td>No.2→No.1</td></tr> </table> </div> |  | Temperature | Duration | 1 | $-25 \pm 3^\circ\text{C}$<br>(Thermostat No.1) | 30 min. | 2 | Standard atmospheric | No.1→No.2 | 3 | $85 \pm 2^\circ\text{C}$<br>(Thermostat No.2) | 30 min. | 4 | Standard atmospheric | No.2→No.1 |
|                                                                                                            | Temperature                                                                   | Duration                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| 1                                                                                                          | $-25 \pm 3^\circ\text{C}$<br>(Thermostat No.1)                                | 30 min.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| 2                                                                                                          | Standard atmospheric                                                          | No.1→No.2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| 3                                                                                                          | $85 \pm 2^\circ\text{C}$<br>(Thermostat No.2)                                 | 30 min.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| 4                                                                                                          | Standard atmospheric                                                          | No.2→No.1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| Moisture storage                                                                                           | $\Delta L/L_o \leq \pm 5\%$<br><br>There shall be no mechanical damage.       | The sample shall be left for $96 \pm 4$ hours in a temperature of $40 \pm 2^\circ\text{C}$ and a humidity(RH) of 90~95%.<br><br>Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity more than 1 hour.                                                                                                                                                                                                                                                                                                                                                                                              |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |
| Test conditions :<br><br>The sample shall be reflow soldered onto the printed circuit board in every test. |                                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |  |             |          |   |                                                |         |   |                      |           |   |                                               |         |   |                      |           |

## Taping Dimensions(Unit:mm)



| TYPE    | W      | A        | B         | C     | D        | E        | P      | K<br>Ref | T         | MPQ |
|---------|--------|----------|-----------|-------|----------|----------|--------|----------|-----------|-----|
| MPO5022 | 32±0.3 | 15.7±0.1 | 18.95±0.1 | 16.05 | 14.2±0.1 | 7.20±0.1 | 20±0.1 | 7.40     | 0.35±0.05 | 250 |

## Reel Dimensions(Unit:mm)



| TYPE    | W       | W1        | W2      | W3       | A         | B         | C        | D       |
|---------|---------|-----------|---------|----------|-----------|-----------|----------|---------|
| MPO5022 | 330±2.0 | 32.4±1.50 | 38.4MAX | 31.9 Min | 13.0±0.50 | 21.0±0.80 | 2.0±0.50 | 100 Min |

## Direction of rolling

