

TBY-C3-UNIV-SP-2KS-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Analogue interfaces are equipped with 40-pole connectors (KS). Versions are available with disconnecting plugs and test points which are extremely useful for voltage and current measurements. There are also versions with useful additional pins for customers who wish to incorporate other elements (resistor ...) for converting voltage/current or monitoring the current loop.

General ordering data

Version	Interface, RS, 2 x KS (40P), LL2N 5.08 mm
Order No.	1371640000
Type	TBY-C3-UNIV-SP-2KS-S
GTIN (EAN)	4050118206791
Qty.	1 pc(s).

TBY-C3-UNIV-SP-2KS-S
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Technical data
Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	109 mm	Height (inches)	4.291 inch
Width	112 mm	Width (inches)	4.409 inch
Net weight	220.6 g		

Temperatures

Storage temperature	-40...85 °C	Operating temperature	-25...70 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	9dd73319-d286-43a8-a0b7-6458fd2c03f9
------------	----------------	------	--------------------------------------

General data

LED status display per channel	No	Disconnection per channel	No
Type of test point	Soldering tags	Switch	No
Fuse per channel	No	LED status of the supply voltage	No
Power supply fuse	No		

Connection data

Connection (field side)	LL2N 5.08 mm	Connection on control side	2 x KS (40P)
Number of poles (control side)	40-pole plug		

Ratings data

Operating voltage	50 V AC / 70 V DC	Max. current per channel	1 A
-------------------	-------------------	--------------------------	-----

Insulation coordination (EN50178)

Rated insulation voltage	< 50 V AC	Surge voltage category	III
Pollution severity level	2	Pulse voltage test (1,2/50µs)	0.8 kV
Insulation test voltage	0.35 kVAC		

Connection field

Clamping range, max.	6 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Max. wire cross-section, AWG	AWG 12	Min. wire cross-section, AWG	AWG 26
Sleeve with plastic collar, max.	2.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Type of connection	Screw connection		

TBY-C3-UNIV-SP-2KS-S
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Technical data
Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	2.5 mm ²
Flexible with sleeve, min.	2.5 mm ²	Ferrule with plastic collar, max.	0.5 mm ²
Wire cross-section, min. AWG	AWG 12	Wire cross-section, max. AWG	AWG 26
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-14-11-52	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

Approvals

Approvals


Downloads

Product Change Notification	20210602 Technical change to TBY interfaces
Catalogues	Catalogues in PDF-format
Brochures	

TBY-C3-UNIV-SP-2KS-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

