


MALE PCB PINS

SOLDER TERMINALS VARIOUS TYPES

2709

2709-X-07-XX-00-00-07-0

Swage mount in 2,95 hole




Basic Part Number	Board Thickness	Length V	Length A
2709-2	1,57	2,77	7,14
2709-3	2,39	3,58	6,35

8602

8602-1-00-XX-00-00-07-0

Square press-fit in 0,81 plated through-hole




2115

2115-2-00-XX-00-00-07-0

Swage mount in 1,09 hole

For a 1,57 thick board




2326

2326-2-00-XX-00-00-07-0

Swage mount in 1,40 hole


For a 1,57 thick board



8831

8831-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



8835

8835-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



8836

8836-0-00-XX-00-00-03-0

Press-fit in 1,91 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER (60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com