








| 标记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修改<br>REVISE | 日期<br>DATE | 核准<br>APPROVE |
|------------|---------------------------------|--------------|------------|---------------|
|            |                                 |              |            |               |



3D VIEW



SECTION A-A



PAD AREA (TOP VIEW)

## NOTES:

- MATERIAL:
  - HOUSING: LCP ,COLOR IS BLACK;
  - CONTACT: PHOSPHOR COPPER (C5191 T=0.30mm) ;
  - SHELL: BRASS
- FINISH:
  - CONTACT: PLATED OVER NI,GOLD PLATED G/Fu";
  - SHELL:PLATED OVER NI;
- ELECTRICAL:
  - VOLTAGE RATING: 125 VAC RMS;
  - CURRENT RATING: 1.5 AMP;
  - CONTACT RESISTANCE: 35MILLIOHMS MAX.;
  - WITHSTAND VOLTAGE: 500 VAC RMS
- 50(60)Hz,1MIN.;
- INSULATION RESISTANCE: 500MEGOHMS MIN @500V DC.;
- MECHANICAL:
  - MATING/UNMATING FORCE: 22N MAX.;
  - RETENTION STRENGTH: 50N MIN.;
  - OPERATING LIFE: 750 CYCLES MIN.;
- ENVIRONMENTAL:
  - STORAGE TEMPERATURE RANGE: -40°C~+85°C;
  - OPERATION TEMPERATURE RANGE: -25°C~+70°C;
  - SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)

|    |    |     |       |    |
|----|----|-----|-------|----|
| 3  | 外壳 | 铜   | 镀镍    |    |
| 2  | 接触 | 铜   | 镀金G/F |    |
| 1  | 基座 | LCP | 黑色    |    |
| 序号 | 品名 | 材质  | 电镀/颜色 | 备注 |

|                                                 |             |               |               |                  |      |
|-------------------------------------------------|-------------|---------------|---------------|------------------|------|
|                                                 | 深圳市虹成电子有限公司 |               | 品名<br>TITLE   | 网口               |      |
|                                                 |             |               | 料号<br>PART NO | HC-WK88-H865T-QB |      |
| UNLESS GENERAL TOLERANCE:                       |             | 比列<br>SCALE   | 1:1           |                  |      |
| X. xxx ±0.10<br>X. xx ±0.20<br>X. x ±0.30       |             | 单位<br>UNIT    | MM            | 制图<br>DRAW       | AhYe |
| ANGULAR:<br>X. xx° ±1°<br>X. x° ±3°<br>X. ° ±5° |             | 张数<br>PART NO | 1 OF 1        | 审核<br>CHECKED    | 夏操云  |
|                                                 |             | 版本<br>REV     | A             | 批准<br>APPROVE    | 赵亮亮  |