


LBC817-40WT1G

NPN Silicon General Purpose Transistors


1. FEATURES

- We declare that the material of product compliance with RoHS requirements and Halogen Free.



2. DEVICE MARKING AND ORDERING INFORMATION

Device	Marking	Shipping
LBC817-40WT1G	YM	3000/Tape&Reel
LBC817-40WT3G	YM	10000/Tape&Reel



3. MAXIMUM RATINGS(Ta = 25°C)

Parameter	Symbol	Limits	Unit
Collector–Emitter Voltage	VCEO	45	V
Collector–Base Voltage	VCBO	50	V
Emitter–Base Voltage	VEBO	5	V
Collector Current(Continuous)	IC	500	mA
Junction Temperature	TJ	-55~+150	°C
Storage Temperature	Tstg	-55~+150	°C

4. THERMAL CHARACTERISTICS





Parameter	Symbol	Limits	Unit
Total Device Dissipation, FR-4 Board (Note 1) @ TA = 25°C Derate above 25°C	PD	300 2.4	mW mW/°C
Thermal Resistance, Junction–to–Ambient(Note 1)	RθJA	417	°C/W

1. 30.0mm×25.0mm×1.6mm(FR4), Copper foil thickness 35μm;



5. ELECTRICAL CHARACTERISTICS (Ta= 25°C)

Characteristic	Symbol	Min.	Typ.	Max.	Unit
OFF CHARACTERISTICS					
Collector–Emitter Breakdown Voltage (IC = 10 mA)	V(BR)CEO	45	-	-	V
Collector–Emitter Breakdown Voltage (IC = 10 μ A, VEB = 0)	V(BR)CES	50	-	-	V
Emitter–Base Breakdown Voltage (IE = 1.0 μ A)	V(BR)EBO	5	-	-	V
Collector Cutoff Current (VCB = 20 V) (VCB = 20 V, TA = 150°C)	ICBO	- -	- -	100 5	nA μ A
ON CHARACTERISTICS					
DC Current Gain (IC = 100 mA, VCE = 1.0 V) (IC = 500 mA, VCE = 1.0 V)	hFE	250 40	- -	600 -	
Collector–Emitter Saturation Voltage (IC = 500 mA, IB = 50 mA)	VCE(sat)	-	-	0.7	V
Base–Emitter Voltage (IC = 500 mA, VCE = 1.0 V)	VBE(on)	-	-	1.2	V
SMALL–SIGNAL CHARACTERISTICS					
Current–Gain — Bandwidth Product (IC = 10 mA, VCE = 5.0 V, f = 100 MHz)	fT	100	-	-	MHz
Output Capacitance (VCB = 10 V, f = 1.0 MHz)	Cobo	-	10	-	pF


6.ELECTRICAL CHARACTERISTICS CURVES



6.ELECTRICAL CHARACTERISTICS CURVES(Con.)




7.OUTLINE AND DIMENSIONS



SC70			
DIM	MIN	NOR	MAX
A	0.80	0.95	1.00
A1	0.00	0.05	0.10
A2	0.7 REF		
b	0.30	0.35	0.40
c	0.10	0.15	0.25
D	1.80	2.05	2.20
E	1.15	1.30	1.35
e	1.20	1.30	1.40
e1	0.65 BSC		
L	0.20	0.35	0.56
He	2.00	2.10	2.40
ALL Dimension in mm			

8.SOLDERING FOOTPRINT



SC70	
DIM	MIN
A	1.90
B	0.65
C	0.65
X	0.70
Y	0.90

DISCLAIMER

- Curve guarantee in the specification. The curve of test items with electric parameter is used as quality guarantee. The curve of test items without electric parameter is used as reference only.
- Before you use our Products for new Project, you are requested to carefully read this document and fully understand its contents. LRC shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any LRC's Products against warning, caution or note contained in this document.
- All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using LRC's Products, please confirm the latest information with a LRC sales representative.