

SMD Transformers for Flyback Applications

FC-SLF6030 –330

Small size


- Flyback transformers
- Coupled inductors in SEPIC applications
- Common mode filter chokes.

Ambient temperature -40°C to $+85^{\circ}\text{C}$




Storage temperature Component: -40 °C to +125 °C



1. Dimensions:mm



2.Schematic:



SMD Transformers for Flyback Applications

FC-SLF6030-330


4. ELECTRIC CHARACTERICS

Part Number	Turns Ration	Current Rating ₂ (mA)	Inductance (uH)	RDC (Ω)	Hi-Pot (Vdc) 5mA/3S
				1-2 4-3	
FC-SLF6030-330	1:1	670	33 ±20%	0.95	1000


Electrical Specifications @ 25°C — Operating Temperature -40°C to +125°C .

- (1).Rated Current: Base on temp.rise & $\Delta L/L_{0A} \leq 30\%$ Max and $\Delta T = 40^\circ\text{C}$ Typ
- (2).Operating Temperature: -40°C up to +125°C
- (3).Storage Temperature: -20°C up to +40°C, 75% RH max.

5. Typical Flyback Converter



6. Typical Buck Converter with auxiliary output



8. Typical SEPIC schematic

