

## General Description

The WSL60N65 is CoolFET II MOSFET family that is utilizing charge balance technology for extremely low on-resistance and low gate charge performance.

WSL60N65 is suitable for applications which require superior power density and outstanding efficiency

## Features

- High ruggedness
- Fast switching
- 100% avalanche tested
- Improved dv/dt capability


## Product Summary

$BV_{DSS}$	$R_{DS(ON)}$	$I_D$
650V	150mΩ	60A

## Applications

- Uninterruptible Power Supply(UPS)
- Power Factor Correction (PFC)

## TO-247-3L Pin Configuration



## Absolute Maximum Ratings ( $T_C=25^{\circ}\text{C}$ , Unless Otherwise Noted)

Symbol	Parameter	Rating	Units
$V_{DS}$	Drain-Source Voltage	650	V
$V_{GS}$	Gate-Source Voltage	$\pm 30$	V
$I_D$	Continuous Drain Current	60	A
$I_{DM}$	Pulsed Drain Current <sup>1</sup>	142	A
$E_{AS}$	Single Pulse Avalanche Energy <sup>2</sup>	500	mJ
$P_D$	Power Dissipation ( $T_C=25^{\circ}\text{C}$ )	151	W
$T_{STG}$	Storage Temperature Range	-55 to 150	$^{\circ}\text{C}$
$T_J$	Operating Junction Temperature Range	-55 to 150	$^{\circ}\text{C}$

## Thermal Data

Symbol	Parameter	Typ.	Max.	Units
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	---	62	$^{\circ}\text{C/W}$
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	---	0.82	$^{\circ}\text{C/W}$

**Electrical Characteristics** ( $T_J=25^{\circ}\text{C}$ , Unless Otherwise Noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Units
$BV_{DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V$ , $I_D=250\mu A$	650	---	---	V
$\Delta BV_{DSS}/\Delta T_J$	$BV_{DSS}$ Temperature Coefficient	$I_D=250\mu A$ , Reference $25^{\circ}\text{C}$	---	0.7	---	$V/^{\circ}\text{C}$
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$ , $I_D=3.2A$	---	150	190	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$ , $I_D=250\mu A$	2.5	3.3	4.5	V
$I_{DSS}$	Drain-Source Leakage Current	$V_{DS}=650V$ , $V_{GS}=0V$	---	---	1.0	$\mu A$
		$V_{DS}=520V$ , $T_C=125^{\circ}\text{C}$	---	---	50	
$I_{GSS}$	Gate-Source Leakage Current	$V_{DS}=0V$ , $V_{GS}=\pm 30V$	---	---	$\pm 100$	nA
$Q_g$	Total Gate Charge	$V_{DS}=480V$ , $V_{GS}=10V$ , $I_D=11A$	---	7.27	---	nC
$Q_{gs}$	Gate-Source Charge		---	17.4	---	
$Q_{gd}$	Gate-Drain Charge		---	43.9	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DS}=400V$ , $I_D=13A$ $R_G=4.7\Omega$ , $V_{GS}=13V$	---	10	---	ns
$T_r$	Rise Time		---	19.8	---	
$T_{d(off)}$	Turn-Off Delay Time		---	45.4	---	
$T_f$	Fall Time		---	41.4	---	
$C_{iss}$	Input Capacitance	$V_{DS}=100V$ , $V_{GS}=0V$ , $f=1.0\text{MHz}$	---	1510	---	pF
$C_{oss}$	Output Capacitance		---	65	---	
$C_{rss}$	Reverse Transfer Capacitance		---	2.4	---	

**Diode Characteristics**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Units
$I_S$	Continuous Source Current	$V_D=V_G=0V$ , Force Current	---	---	60	A
$I_{SM}$	Pulsed Source Current		---	---	180	A
$V_{SD}$	Diode Forward Voltage	$V_{GS}=0V$ , $I_S=7.3A$	---	0.812	1.5	V
$t_{rr}$	Reverse Recovery Time	$V_{GS}=0V$ , $I_S=11A$ , $V_{DD}=400V$	---	288	---	ns
$Q_{rr}$	Reverse Recovery Charge	$di_F/dt=100A/\mu s$	---	3.66	---	$\mu C$

**Note:**

1. The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 20Z copper.
2. The  $E_{AS}$  data shows Max. rating .  $L=0.5mH$ ,  $I_{AS}=7A$ ,  $V_{DD}=50V$ ,  $R_G=25\Omega$
3. The test condition is Pulse Test:  $I_{SD} \leq I_D$ ,  $di/dt = 100A/\mu s$ ,  $V_{DD} \leq BV_{DSS}$ , Starting at  $T_J=25^{\circ}\text{C}$
4. The power dissipation is limited by  $150^{\circ}\text{C}$  junction temperature
5. The data is theoretically the same as  $I_D$  and  $I_{DM}$ , in real applications, should be limited by total power dissipation.

## Typical Characteristics




Figure1: Power dissipation (Non FullPAK)




Figure2: Power dissipation (FullPAK)




Figure3: Power dissipation  
 $P_{tot}=f(T_c)$




Figure4: Max. transient thermal impedance  
 $Z_{thJC}=f(t_p)$ ; parameter:  $D= t_p/T$




Figure5: Max. transient thermal impedance  
 $Z_{thJC}=f(t_p)$ ; parameter:  $D= t_p/T$






Figure6: Max. transient thermal impedance  
 $Z_{thJC}=f(t_p)$ ; parameter:  $D= t_p/T$

## Typical Characteristics (Cont.)




**Figure 7: Safe operating area (Non FullPAK)**

$I_D = f(V_{DS})$ ;  $T_J = 25^\circ\text{C}$ ;  $D = 0$ ; parameter:  $t_p$




**Figure 8: Safe operating area (Non FullPAK)**

$I_D = f(V_{DS})$ ;  $T_J = 25^\circ\text{C}$ ;  $D = 0$ ; parameter:  $t_p$




**Figure 9: TSafe operating area (FullPAK-TO220A)**

$R_{DS(on)} = f(I_D)$ ;  $T_J = 25^\circ\text{C}$ ; parameter:  $V_{GS}$




**Figure 10: Typ. output characteristics**

$R_{DS(on)} = f(T_J)$ ;  $I_D = 3.2\text{A}$ ;  $V_{GS} = 10\text{V}$



**Figure 11: Typ. output characteristics**


$I_D = f(V_{DS})$ ;  $T_J = 125^\circ\text{C}$ ; parameter:  $V_{GS}$



**Figure 12: Type. gate charge**

$R_{DS(on)} = f(I_D)$ ;  $T_J = 25^\circ\text{C}$ ; parameter:  $V_{GS}$

## Packaging information



Symbol	Millimeters		
	Min.	Nom.	Max.
A	4.80	5.00	5.20
A1	2.21	2.41	2.61
A2	1.85	2.00	2.15
b	1.11	1.21	1.36
b2	1.91	2.01	2.21
b4	2.91	3.01	3.21
c	0.51	0.61	0.75
D	20.70	21.00	21.30
D1	16.25	16.55	16.85
E	15.50	15.80	16.10
E1	13.00	13.30	13.60
E2	4.80	5.00	5.20
E3	2.30	2.50	2.70
e	5.44 BSC		
L	19.62	19.92	20.22
L1	-	-	4.30
P	3.40	3.60	3.80
P1	-	-	7.30
S	6.15 BSC		

## Attention

- 1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.
- 2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.
- 3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- 4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- 5, In the event that any or all Winsok power products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- 6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.
- 7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- 8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement,etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you intend to use.
- 9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.