


GT-TS201X-H0065-LX



G-Switch

Operating Force


A=180gf
B=250gf
C=100gf

Switch Height
H0065=0.65mm

Switch Lifetime
L1=100,000 Cycles
L3=300,000 Cycles




RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05



CIRCUIT DIAGRAM

5	BUTTON	HIGH TEMPERATURE PLASTIC	BLACK
4	TAPE	POLYIMIDE	TRANSPARENT
3	CONTACT	STAINLESS STEEL	Ag PLATING
2	TERMINAL	COPPER ALLOY	Ag PLATING
1	BASE	HIGH TEMPERATURE PLASTIC	BLACK
NO.	PART NAME	MATERIAL	REMARK



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.20
X.x ±0.15
X.xx ±0.10
X* ±2°

Title: Vertical Tact Switch SMT 2.8×1.9×H0.65mm			
Molde Code: GT-TS201X-H0065-LX			
DRAWN	CHECKED	APPROVED	DATE
Jiang	Xia	Chen	2023.02.01

品赞科技®
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1