


### 1. External Dimensions (Unit:m/m)



Type	A	B	C	D Typ.	E Typ.	F Typ.	G Typ.	H Typ.	Q'TY/Reel
APS04D20	4.0±0.3	4.8Max	2.0Max	1.5	0.8	5.2	2.5	2.2	3000

### 2. Part Number Code

APS	04	D	20	LC	M	4R7
Series Name	Dimensions: L*W	Materials	Dimensions: H	Internal controls	Tolerance ±20%	Inductance

### 3. Electrical Characteristics

Part Number	Inductance (uH)	Test Conditions	DC Resistance (mΩ) Max.	DC Current Irms(A) Typ.	DC Current Isat(A) Typ.
APS04D20LCM4R7	4.7	100K Hz/1V	104	2.82	3.03

#### Notes:

- 1) All test data is referenced to 25°C ambient.
- 2) Absolute maximum voltage 30V DC.
- 3) Operating temperature range -40°C to +125°C(Including self - temperature rise).
- 4) Irms :DC current(A) that will cause an approximate ΔT of 40°C.
- 5) Isat :DC current(A) that will cause I<sub>o</sub> to drop approximately 40%.
- 6) The part temperature(ambient + temp rise)should not exceed 125°C under worst case operating conditions. Circuit design and other cooling provisions all affect the part temperature, part temperature should be verified in the end application.