




Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION		DWN	CHK
A		DESIGN		James	
					9/26


220±10

NOTES:

1. ELECTRICAL:
- 1.1. VOLTAGE RATING:DCV 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
- 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	OD:3.5* 15 mm 套管	2
③	接头	SMB公头公针, 直头, 镀金	
②	接头	SMB母头母针, 直头, 镀金	2
①	同轴线	RG1.37黑色线, OD:1.37mm	AS

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRON CO., LTD.

ALL DIMENSION ARE IN MM	DRAWN James	DATE 2025-03-10	TITLE KH-SMBJ-SMBK-RG1.37-220MM		
	CHKD. Frank	2025-03-10			
	APPD. Scott	2025-03-10			
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING			SIZE DWG Number.		REV A
PROJECTION 	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150		B		
			SCALE: Free	TYPE	SHEET 1 OF 1