





Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		9/26

60±5



NOTES:

- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- MATERIAL:
 - SEE TABLE
- ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	OD:3.5* 15 mm 套管	2
③	接头	SMB母头母针, 直头, 镀金	
②	接头	SMB母头母针, 直头, 镀金	2
①	同轴线	RG316棕色线, OD:2.5mm	AS

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRON CO., LTD.

ALL DIMENSION ARE IN MM	DRAWN James	DATE 2025-03-10	TITLE KH-SMBK-SMBK-RG316-60MM
	CHKD. Frank	2025-03-10	
	APPD. Scott	2025-03-10	
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING			SIZE DWG Number.
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1' ±0.3 ±0.25 ±0.150		REV A
SCALE:Free		TYPE	SHEET 1 OF 1

CUSTOMER P/N: