

零件承认书

SPECIFICATION FOR APPROVAL

客户名称： 0110

规格描述： ZNR6045磁胶电感规格书

日 期： 2023/10/10

增益签核：

制订	审核	核准
夏琳	陈雨	李万

客户签核：

工程	审核	核准



东莞市增益实业有限公司

地址：东莞市塘厦镇林村塘厦大道北552号

电话：0769-87321000

传真：0769-87891229

物料类型： 磁胶电感

日 期： 2023/10/10

版 本： A



◆特征:

- 磁性胶水涂敷结构极大减少了蜂鸣声
- 大电流低直流阻抗
- 直接在磁芯上金属化电极,抗跌落冲击强
经久耐用
- 闭合磁路结构设计,漏磁少,抗 EMI 能力强
- 省空间,更省电
- 符合 RoHS,无卤和 REACH

◆用途:

- 广泛应用于 LED 背光板、平板电视、
蓝光 DVD 机顶盒、笔记本电脑、台式电脑、
服务器、显卡、便携式游戏机、个人导航系统、
多媒体、汽车产品、通信设备、直流转换。

◆环境:

- 工作温度: -40°C 至 $+125^{\circ}\text{C}$
(包括线圈自身温升)

◆试验设备:

- 电感值: HP4284A, HP4285A 或同等仪器
- 电流: HP4284+42841A
- 直流电阻: Chroma 16502 或同等仪器

◆产品型号:

Features:

- Magnetic-resin shielded construction reduces buzz
Noise to ultra-low levels
- Large Current and Low DCR
- Metallization on Ferrite Core results in excellent shock
Resistance and damage-free durability
- Closed magnetic circuit design reduces leakage
Flux and Electro Magnetic Interference (EMI)
- Takes up less PCB real estate and save more power
Small parasitic capacitance
- RoHS, Halogen Free and REACH Compliance

Applications:

- LED backlight、Flat-screen TVs, blue-ray disc
Set top box、Notebooks, desktop computers, servers,
Graphic cards、Portable gaming devices, personal
Navigation systems, personal multimedia devices,
Automotive systems Telecomm base station、DC-DC
Converter

Environmental Data:

- Operating Temperature: -40°C to $+125^{\circ}\text{C}$
(Including coils self-temperature rise)

Test Equipment:

- L: HP4284A or HP4285A LCR meter or equivalent
- Isat & Irms: HP4284+42841A
- DCR: Chroma 16502 or equivalent

Product Identification:

ZNR

①

8040

②

ST

③

100

④

M

⑤

①	
类型 Type	
ZNR	闭磁路贴片磁胶电感 Shielded SMT Power Inductors 

②	
外形尺寸(L×W×H) (mm) External Dimensions (L×W×H) (mm)	
8040	8.0×8.0×4.0

④
Inductance
10 uH

③ Feature Type S: Standard T: 编带


⑤

公差 Inductance Tolerance

K: $\pm 10\%$,M: $\pm 20\%$, N: $\pm 30\%$

◆外观尺寸:

Shape and Dimensions(dimensions are in mm):



Part No	ITEM								
	Shap	A	B	C	D	E	F	G	H
ZNR6045S	Fig.2	6.0 $\pm$ 0.3	6.0 $\pm$ 0.3	4.5 Max	2.9 $\pm$ 0.3	4.9 $\pm$ 0.3	1.7 Typ	2.8 Typ	5.7 Typ

◆规格特性:

Specifications:

● ZNR6045 Series

Part Number	Inductance (uH) @100KHz	DC Resistance (Ω)		额定电流	饱和电流
		Typ.	Max.	Current (A)	Current (A)
ZNR6045STR47N	0.47	0.006	0.008	6.60	16.500
ZNR6045STR56N	0.56	0.006	0.008	7.50	15.000
ZNR6045STR68N	0.68	0.006	0.008	6.50	12.000
ZNR6045STR82N	0.82	0.008	0.010	6.50	11.000
ZNR6045ST1R0M	1.00	0.011	0.014	5.60	10.000
ZNR6045ST1R5M	1.50	0.012	0.016	5.40	9.700
ZNR6045ST1R8N	1.80	0.012	0.016	5.40	8.400
ZNR6045ST2R2M	2.20	0.014	0.018	5.00	7.400
ZNR6045ST2R7N	2.70	0.015	0.020	4.70	6.300
ZNR6045ST3R0N	3.00	0.020	0.026	4.20	6.200
ZNR6045ST3R3N	3.30	0.021	0.027	4.00	6.200
ZNR6045ST3R6N	3.60	0.021	0.027	4.00	5.700
ZNR6045ST4R7M	4.70	0.026	0.034	3.60	5.500
ZNR6045ST5R6M	5.60	0.029	0.038	3.40	4.600
ZNR6045ST6R2M	6.20	0.031	0.040	3.30	4.800
ZNR6045ST6R8M	6.80	0.031	0.040	3.30	4.300
ZNR6045ST7R5M	7.50	0.034	0.044	3.20	3.800
ZNR6045ST8R2M	8.20	0.043	0.056	2.80	4.300
ZNR6045ST9R1M	9.10	0.043	0.056	2.80	3.700
ZNR6045ST100M	10.0	0.048	0.062	2.70	3.500
ZNR6045ST120M	12.0	0.058	0.075	2.40	3.000
ZNR6045ST150M	15.0	0.068	0.088	2.20	2.700
ZNR6045ST180M	18.0	0.081	0.105	2.00	2.400

◆规格特性:

Specifications:

● ZNR6045 Series

Part Number	Inductance (uH) @100KHz	DC Resistance (Ω)		额定电流	饱和电流
		Typ.	Max.	Current (A)	Current (A)
ZNR6045ST220M	22.0	0.089	0.116	2.00	2.200
ZNR6045ST270M	27.0	0.102	0.133	1.80	2.100
ZNR6045ST300M	30.0	0.132	0.172	1.60	1.800
ZNR6045ST330M	33.0	0.137	0.178	1.60	1.800
ZNR6045ST360M	36.0	0.173	0.225	1.50	1.800
ZNR6045ST390M	39.0	0.180	0.234	1.40	1.600
ZNR6045ST430M	43.0	0.200	0.260	1.30	1.800
ZNR6045ST470M	47.0	0.200	0.260	1.30	1.500
ZNR6045ST510M	51.0	0.207	0.269	1.20	1.500
ZNR6045ST560M	56.0	0.221	0.287	1.20	1.400
ZNR6045ST620M	62.0	0.235	0.306	1.20	1.400
ZNR6045ST680M	68.0	0.289	0.376	1.10	1.300
ZNR6045ST750M	75.0	0.305	0.397	1.00	1.200
ZNR6045ST820M	82.0	0.341	0.443	0.99	1.100
ZNR6045ST910M	91.0	0.359	0.467	0.94	1.100
ZNR6045ST101M	100	0.433	0.563	0.88	1.000
ZNR6045ST121M	120	0.484	0.629	0.85	0.940
ZNR6045ST151M	150	0.580	0.754	0.77	0.880
ZNR6045ST221M	220	0.834	1.084	0.65	0.770
ZNR6045ST271M	270	1.096	1.425	0.63	0.650
ZNR6045ST331M	330	1.270	1.651	0.63	0.630
ZNR6045ST391M	390	1.800	2.340	0.48	0.560
ZNR6045ST471M	470	1.800	2.340	0.48	0.560

◆规格特性:

Specifications:


● ZNR6045 Series

Part Number	Inductance (uH) @100KHz	DC Resistance (Ω)		额定电流	饱和电流
		Typ.	Max.	Current (A)	Current (A)
ZNR6045ST561M	560	2.480	3.224	0.38	0.460
ZNR6045ST681M	680	2.500	3.250	0.38	0.460
ZNR6045ST751M	750	3.700	4.810	0.35	0.400
ZNR6045ST821M	820	3.700	4.810	0.35	0.360
ZNR6045ST102M	1000	4.500	5.850	0.35	0.350
ZNR6045ST152M	1500	6.750	8.100	0.24	0.270
ZNR6045ST202M	2000	9.700	11.640	0.200	0.230
ZNR6045ST222K	2200	10.000	12.000	0.200	0.230
ZNR6045ST252M	2500	10.570	12.680	0.170	0.200
ZNR6045ST332K	3300	13.000	15.300	0.170	0.200
ZNR6045ST472K	4700	18.750	22.500	0.140	0.170
ZNR6045ST502M	5000	20.000	24.000	0.110	0.140
ZNR6045ST602M	6000	30.000	36.000	0.110	0.140
ZNR6045ST682K	6800	31.200	37.400	0.110	0.140
ZNR6045ST702M	7000	33.000	39.600	0.100	0.120
ZNR6045ST802M	8000	35.500	42.600	0.100	0.120
ZNR6045ST103K	10000	40.000	48.000	0.10	0.120
ZNR6045ST123K	12000	62.000	74.400	0.080	0.110
ZNR6045ST143K	14000	63.500	76.200	0.070	0.100
ZNR6045ST153K	15000	70.000	84.000	0.070	0.100

- ※ The saturation current value is the DC current value having inductance decrease down to 30%.(at 20℃)
- ※ The temperature rise current value is the DC current value having temperature increase up to 40℃. (at 20℃)
- ※ The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.




■ Taping Dimensions(Unit:mm)



TYPE	Chip Thickness	W	A	B	D	P	K Max	T Max	MPQ
ZNR6045	4.50	16.0	6.40	6.40	7.50	8.00	4.70	0.40	1500


■ Reel Dimensions(Unit:mm)




TYPE	W	W1	A	B	C	D
ZNR6045	330±2.0	16.5±1.50	13.0±0.50	21.0±0.80	2.0±0.50	100 Min



■ Direction of rolling



■ Cover tape peel off condition



Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed 300 ± 10 mm/min.

使用注意事项

REMINDERS FOR USING THESE PRODUCTS



- 保存时间为12 个月以内，保存条件（温度5~40°C以下、湿度35 ~ 66%RH 以下），需充分注意。
若超过保存时间，端子电极的可焊性将可能老化。

The storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5~40°C, humidity: 35 to 65% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate.

- 请勿在气体腐蚀环境（盐、酸、碱等）下使用和保存。

Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).

- 手上的油脂会导致可焊性降低，应避免用手直接接触端子。

Don't touch electrodes directly with bare hands as oil secretions may inhibit soldering. Always ensure optimum conditions for soldering.

- 请小心轻拿轻放,避免由于产品的跌落或取出不当而导致的损坏。

Please always handle products carefully to prevent any damage caused by dropping down or inappropriate removing.

- 端子过度弯曲会导致断线,请不要过度弯曲端子。

Don't bend the terminals with excessive stress in case of any wire fracture.

- 不要清洗产品，如需要清洗时请联系我司。

Don't rinse coils by yourself and please contact ZE if necessary.

- 请勿将本产品靠近磁铁或带有磁力的物体

Don't expose the products to magnets or magnetic fields

- 在实施焊接前，请务必进行预热。预热温度与焊接温度及芯片温度的温度差要在150°C 以内。

Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.

- 安装后的焊接修正应在规格书规定的条件范围内。若加热过度可能导致短路、性能降低、寿命减少。

Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.

- 装置会因通电而自我发热（温度上升），因此在热设计方面需留有充分余地。

Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.

- 非磁屏蔽型在基板设计时需注意配置线圈，受到电磁干扰可能会导致误动作。

Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.

- 当本公司产品使用在一般电子设备以外的场合,如:车载,医疗设备,军用,航空航天等,请务必联系本公司营业部门,如超出本公司产品使用条件而引起的机器故障时,本公司概不负责。

If ZE product will be applied in area like automotive product, medical equipment, military and aerospace except general electronic device, please keep ZE sales informed in advance. ZE shall not be held liable for any malfunction or breakdown caused by using product in the condition which is inconsistent with that recommended by ZE.