




SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

 深圳市韩下电子有限公司					No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
					1	0.00	2.00	11	20.00	22.00	21	40.00	42.00	31	60.00	62.00
					2	2.00	4.00	12	22.00	24.00	22	42.00	44.00	32	62.00	64.00
					3	4.00	6.00	13	24.00	26.00	23	44.00	46.00	33	64.00	66.00
					4	6.00	8.00	14	26.00	28.00	24	46.00	48.00	34	66.00	68.00
					5	8.00	10.00	15	28.00	30.00	25	48.00	50.00	35	68.00	70.00
					6	10.00	12.00	16	30.00	32.00	26	50.00	52.00	36	70.00	72.00
					7	12.00	14.00	17	32.00	34.00	27	52.00	54.00	37	72.00	74.00
					8	14.00	16.00	18	34.00	36.00	28	54.00	56.00	38	74.00	76.00
					9	16.00	18.00	19	36.00	38.00	29	56.00	58.00	39	76.00	78.00
					10	18.00	20.00	20	38.00	40.00	30	58.00	60.00	40	78.00	80.00

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : $\pm5^\circ$
X.X : ±0.25 X.X° : $\pm1^\circ$
X.XX : ±0.20 X.XX° : $\pm0.5^\circ$

DRAWN NAME:

HX PM2.0-2x5P WT

SIZE	A4	SCALE	N:1	PROUCT NO.
REV	A	UNIT	mm	PROJECT



PAGE 1/1

DRAW : 黄彬 2023/03/21

CHECKED : 张伟 2023/03/21

APPROVED : 罗小春 2023/03/21