








6 5 4

申明：凡是没有产品料号或有“PRELIMINARY”标示的产品图均为临时图面暂不能生产
DECLARATION: ALL PRODUCT DRAWINGS WITHOUT THE PART NUMBER OR
WITH “PRELIMINARY” LABEL ARE TEMPORARY DRAWINGS CAN NOT BE PRODUCED

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	---	INITIAL RELEASED	2022.03.08	Neo.Liu



NOTE:

1.MATERIAL SPECIFICATION:

1.HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0.

2.CONTACTS: COPPER ALLOY

3.MID PLATE: STAINLESS STEEL

4.FRONT SHELL: STAINLESS STEEL

5.EMI PLATE: STAINLESS STEEL

2.PLATING SPECIFICATION:

2-1.CONTACTS:

Ni 50u" MIN. UNDER PLATED OVER ALL.

Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.

(GOLD PLATING THICKNESS FOLLOW THE P/N)

PLATING SPECIFICATIONS OF THE SOLDER AREA FOLLOW THE P/N

2-2.FRONT SHELL:

Ni 30u" MIN. UNDER PLATED OVER ALL.

2-3.MID PLATE:

Ni 30u" MIN. UNDER PLATED OVER ALL.

Sn 80u"MIN. PLATED OVER ALL

2-4.EMI PLATE:

CLEAR ONLY

3.MECHANICAL PERFORMANCE,

3-1.INSERTION FORCE: 0.5~2.0kgf.

3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.

3-3.DURABILITY: 10000 CYCLES.

4.ELECTRICAL PERFORMANCE,

4-1. CURRENT RATING:5.0A

VOLTAGE RATING:5.0V

4-2. LCCR: VBUS & GND PINS AND OTHER PINS: 40mΩ/PIN MAX.

SHIELD: 50mΩ/MAX.

LCCR MAX. CHANGE OF ALL PINS: 10mΩ.

4-3.INSULATION RESISTANCE: 100MΩ MIN

4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.

5. ENVIRONMENTAL PERFORMANCE:

OPERATING TEMPERATURE: -25℃~+85℃.


6.IR REFLOW:

THE PEAK TEMPERATURE ON THE BOARD SHALL

BE MAINTAINED FOR 10 SECONDS AT 260℃.


TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		广东富盈兴业精密科技实业有限公司 Guangdong Fuying Precision Technology Industrial Co.,LTD	
X.X	±0.30	X.X	±10°	PART NO.	---
.XX	±0.20	.X	± 8°		
.XXX	±0.10	.XX	± 5°		
UNITS	mm	DESIGN:	Neo.Liu	DRAWG NO.	FY23-011TC242F279-08
MATERILA	---	CHED:		SCALE	SHEET
FINISH	---	APPD:		1:1	1/3

申明：凡是没有产品料号或有“PRELIMINARY”标示的产品图均为临时图面暂不能生产
DECLARATION: ALL PRODUCT DRAWINGS WITHOUT THE PART NUMBER OR
WITH “PRELIMINARY” LABEL ARE TEMPORARY DRAWINGS CAN NOT BE PRODUCED



USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND







RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS: 0.60MM;DEFAULT TOLERANCE:±0.05

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	---	INITIAL RELEASED	2022.03.08	Neo.Liu

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	广东富盛兴业精密科技实业有限公司 Guangdong Fushengxingye Precision Technology Industrial Co.,LTD.	
X.X	±0.30 X." ±10°	PART NO.	TITLE: USB CF 24PIN SMT TYPE	
.XX	±0.20 X." ± 8°	----	MID-MOUNT 0.8	
.XXX	±0.10 .XX" ± 5°	DESIGN: Neo.Liu	DRAWG NO. F723-011TC242F279-08	
UNITS	mm	CHED:	SCALE SHEET REV.	
MATERILA	----	APPD:	1:1 2/3 A	
FINISH	-----			

申明：凡是没有产品料号或有“PRELIMINARY” 标示的产品图均为临时图面暂不能生产
DECLARATION: ALL PRODUCT DRAWINGS WITHOUT THE PART NUMBER OR
WITH “PRELIMINARY” LABEL ARE TEMPORARY DRAWINGS CAN NOT BE PRODUCED



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	---	INITIAL RELEASED	2022.03.08	Neo.Liu

CONNECTOR (PCS)		REEL	CARTON
		900	9000
TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	
X.X	±0.30 X.X	±10'	广东富盈兴业精密科技实业有限公司 Guangdong FUYU Precision Technology Industrial Co.,LTD.
.XX	±0.20 .X'	± 8'	
.XXX	±0.10 .XX'	± 5'	
UNITS	mm	DESIGN: Neo.Liu	DRAWG NO. FY23-011TC242F279-08
MATERILA	----	CHED:	
FINISH	-----	APPD:	
		SCALE	SHEET
		1:1	3/3
		REV.	A