






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN


NOTES:

SPECIFICATION:

- CURRENT RATING: 5A MAX
- VOLTAGE: 100 VAC
- TEMPERATURE RANGE: -30 °C ~ 85 °C
- CONTACT RESISTANCE: 40 MILLIONHM MAX
- INSULATION RESISTANCE: 100 MEGOHMS MIN.
- INSERTION FORCE: 5N~20N
- UNMATING FORCE: 8N~20N
- DURABILITY: 10,000 CYCLES



CONNECTOR FRONT EDGE
RECOMMENDED PCB LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CCI	B8	SBUS
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBUI	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

TOLERANCE	NAME(INTENDED USE)	CUSTOMER DRAWING	FUOU Guangdong FUOU Precision Electronic Technology Co.,Ltd.
X.X ±0.30	X° ±10°	PART NO.	TITLE: TYPE C 16P母/座板上垫高1.0
.XX ±0.20	X° ±8°		FY23-12TC1622F1735-10
.XXX ±0.10	.XX° ± 5°	DESIGN:	DRAWG NO. FY23-12TC1622F1735-10
UNITS	mm	MATERIAL	FINISH
		CHED:	APPD:
		SCALE	SHEET
		1:1	1/2
		REV.	A