



REV./ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

SPECIFICATION:

- CURRENT RATING: 3.0A MAX
- VOLTAGE: 100 VAC
- TEMPERATURE RANGE: -30 °C ~ 85 °C
- CONTACT RESISTANCE: 40 MILLIONHM MAX
- INSULATION RESISTANCE: 100 MEGOHMS MIN.
- INSERTION FORCE : 5N~20N
- UNMATING FORCE: 8N~20N
- DURABILITY: 10,000 CYCLES

RECOMMENDED PCB LAYOUT(=0.80±0.05)
COMPONENT SIDE GENERAL TOLERANCE:±0.05

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	NAME(INTENDED USE) CUSTOMER DRAWING
X.X ±0.30	X: ±1°	
XX ±0.20	X: ±8°	
XXX ±0.10	XX: ±5°	
UNITS	DESIGN: ZXM	DRAWG NO. FY23-47TC242F4111-03
MATERIAL	CHED:	
FINISH	APRD:	SCALE 1:1 SHEET 1/2 REV. A

CUSTOMER

6

REV.

ECN NO.

DESCRIPTION

DATE

DESIGN

1

2

3

4

5


6

7

E

胶塞图

剖面 A-A



TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	DRAWING NO. F23-47C242F4111-03	DESIGN: ZXW
X.X ±0.30	X. ±10°	PART NO.	TITLE: CM type-c24p立贴公头三脚
.XX ±0.20	.X. ±8°	F23-47C242F4111-03	
.XXX ±0.10	.XX. ±5°		
UNITS	mm		
MATERIAL	-----	CHEM:	DRAWING NO. F23-47C242F4111-03
FINISH	-----	APPD:	SCALE 1:1 SHEET 1/2 REV. A

