

SI7850DP-T1-E3-VB Datasheet

N-Channel 60-V (D-S) MOSFET

PRODUCT SUMMARY	
V_{DS} (V)	60
$R_{DS(on)}$ (Ω) at $V_{GS} = 10$ V	0.024
$R_{DS(on)}$ (Ω) at $V_{GS} = 4.5$ V	0.028
Q_g typ. (nC)	5.2
I_D (A)	15 ^{a, 9}
Configuration	Single




FEATURES

- Halogen-free According to IEC 61249-2-21 Available
- TrenchFET® Power MOSFET
- 100 % R_g Tested
- 100 % UIS Tested


RoHS
 COMPLIANT

APPLICATIONS

- Battery Switch
- DC/DC Converter



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-source voltage	V_{DS}	60	V
Gate-source voltage	V_{GS}	± 20	
Continuous drain current ($T_J = 150$ °C)	I_D	15 ^a	A
		9 ^a	
		10.3 ^{b, c}	
		8.1 ^{b, c}	
Pulsed drain current ($t = 100$ μ s)	I_{DM}	40	
Continuous source-drain diode current	I_S	12 ^a	
		3 ^{b, c}	
Single pulse avalanche current	I_{AS}	15	
Single pulse avalanche energy	E_{AS}	11.3	mJ
Maximum power dissipation	P_D	35.7	W
		22.9	
		3.6 ^{b, c}	
		2.3 ^{b, c}	
Operating junction and storage temperature range	T_J, T_{stg}	-55 to +150	°C
Soldering recommendations (peak temperature) ^c		260	

THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	TYPICAL	MAXIMUM	UNIT
Maximum junction-to-ambient ^b	R_{thJA}	25	35	°C/W
Maximum junction-to-case (drain)	Steady state	R_{thJC}	2.7	3.5







Notes


- a. Package limited
- b. Surface mounted on 1" x 1" FR4 board
- c. $t = 10$ s

SPECIFICATIONS ($T_J = 25^\circ\text{C}$, unless otherwise noted)								
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT	
Static								
Drain-source breakdown voltage	V_{DS}	$V_{GS} = 0 \text{ V}$, $I_D = 250 \mu\text{A}$		60	-	-	V	
V_{DS} temperature coefficient	$\Delta V_{DS}/T_J$	$I_D = 250 \mu\text{A}$		-	33	-	mV/°C	
$V_{GS(\text{th})}$ temperature coefficient	$\Delta V_{GS(\text{th})}/T_J$			-	-4.8	-		
Gate-source threshold voltage	$V_{GS(\text{th})}$	$V_{DS} = V_{GS}$, $I_D = 250 \mu\text{A}$		1	-	2.8	V	
Gate-source leakage	I_{GSS}	$V_{DS} = 0 \text{ V}$, $V_{GS} = \pm 20 \text{ V}$		-	-	100	nA	
Zero gate voltage drain current	I_{DSS}	$V_{DS} = 60 \text{ V}$, $V_{GS} = 0 \text{ V}$		-	-	1	μA	
		$V_{DS} = 60 \text{ V}$, $V_{GS} = 0 \text{ V}$, $T_J = 70^\circ\text{C}$		-	-	10		
On-state drain current ^a	$I_{D(\text{on})}$	$V_{DS} \geq 5 \text{ V}$, $V_{GS} = 10 \text{ V}$		10	-	-	A	
Drain-source on-state resistance ^a	$R_{DS(\text{on})}$	$V_{GS} = 10 \text{ V}$, $I_D = 10 \text{ A}$		-	0.024	-	Ω	
		$V_{GS} = 4.5 \text{ V}$, $I_D = 5 \text{ A}$		-	0.028	-		
Forward transconductance ^a	g_{fs}	$V_{DS} = 10 \text{ V}$, $I_D = 10 \text{ A}$		-	39	-	S	
Dynamic ^b								
Input capacitance	C_{iss}	$V_{DS} = 30 \text{ V}$, $V_{GS} = 0 \text{ V}$, $f = 1 \text{ MHz}$		-	790	-	pF	
Output capacitance	C_{oss}			-	330	-		
Reverse transfer capacitance	C_{rss}			-	14	-		
Total gate charge	Q_g	$V_{DS} = 30 \text{ V}$, $V_{GS} = 10 \text{ V}$, $I_D = 5 \text{ A}$		-	11.1	17	nC	
				-	5.2	8		
Gate-source charge	Q_{gs}	$V_{DS} = 30 \text{ V}$, $V_{GS} = 4.5 \text{ V}$, $I_D = 5 \text{ A}$		-	2.2	-		
Gate-drain charge	Q_{gd}			-	1.1	-		
Gate resistance	R_g	$f = 1 \text{ MHz}$		0.1	0.6	1.2	Ω	
Turn-on delay time	$t_{d(\text{on})}$	$V_{DD} = 30 \text{ V}$, $R_L = 6 \Omega$, $I_D \geq 5 \text{ A}$, $V_{GEN} = 10 \text{ V}$, $R_g = 1 \Omega$		-	7	15	ns	
Rise time	t_r			-	21	40		
Turn-off delay time	$t_{d(\text{off})}$			-	10	20		
Fall time	t_f			-	10	20		
Turn-on delay time	$t_{d(\text{on})}$			-	13	25		
Rise time	t_r	$V_{DD} = 30 \text{ V}$, $R_L = 6 \Omega$, $I_D \geq 5 \text{ A}$, $V_{GEN} = 4.5 \text{ V}$, $R_g = 1 \Omega$		-	25	50		
Turn-off delay time	$t_{d(\text{off})}$			-	10	20		
Fall time	t_f			-	22	45		
Drain-Source Body Diode Characteristics								
Continuous source-drain diode current	I_S	$T_C = 25^\circ\text{C}$		-	15	-	A	
Pulse diode forward current	I_{SM}			-	-	40		
Body diode voltage	V_{SD}	$I_S = 5 \text{ A}$, $V_{GS} = 0 \text{ V}$		-	0.79	1.2	V	
Body diode reverse recovery time	t_{rr}	$I_F = 5 \text{ A}$, $di/dt = 100 \text{ A}/\mu\text{s}$, $T_J = 25^\circ\text{C}$		-	30	60	ns	
Body diode reverse recovery charge	Q_{rr}			-	60	120	nC	
Reverse recovery fall time	t_a			-	15	-	ns	
Reverse recovery rise time	t_b			-	15	-		


Notes

- a. Pulse test; pulse width $\leq 300 \mu\text{s}$, duty cycle $\leq 2\%$
- b. Guaranteed by design, not subject to production testing


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Source-Drain Diode Forward Voltage




Threshold Voltage




Threshold Voltage




Single Pulse Power, Junction-to-Ambient





Power, Junction-to-Case



Safe Operating Area, Junction-to-Ambient


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

Note

a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit


Current Derating ^a

Normalized Thermal Transient Impedance, Junction-to-Ambient

Normalized Thermal Transient Impedance, Junction-to-Foot

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?275480.

DFN5x6_8L_EP1_P PACKAGE OUTLIN



RECOMMENDED LAND PATTERN



UNIT: mm

SYMBOLS	DIMENSIONS IN MILLIMETERS			DIMENSIONS IN INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.90	1.05	1.20	0.033	0.037	0.039
A1	0.00	—	0.05	0.000	—	0.002
b	0.30	0.40	0.50	0.012	0.016	0.020
c	0.15	0.20	0.25	0.006	0.008	0.010
D	4.90	5.05	5.20	0.201	0.205	0.209
D1	4.25	4.35	4.45	0.167	0.171	0.175
E	5.45	5.55	5.65	0.215	0.219	0.222
E1	5.95	6.05	6.15	0.234	0.238	0.242
E2	3.525	3.625	3.725	0.139	0.143	0.147
E3	1.175	1.275	1.375	0.046	0.050	0.054
e	1.27 BSC			0.050 BSC		
L	0.45	0.55	0.65	0.018	0.022	0.026
L1	0	—	0.15	0	—	0.006
L2	0.68 REF			0.027 REF		
θ	0°	—	10°	0°	—	10°

NOTE

1. PACKAGE BODY SIZES EXCLUDE MOLD FLASH AND GATE BURRS.
MOLD FLASH AT THE NON-LEAD SIDES SHOULD BE LESS THAN 6 MILS EACH.
2. CONTROLLING DIMENSION IS MILLIMETER.
CONVERTED INCH DIMENSIONS ARE NOT NECESSARILY EXACT.

Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.