








1. General Characteristics

Dimensions: 70.6LX334.5WX14H mm

Durability: 5,000 cycles min.

2. Electrical Characteristics

Contact resistance: $50\,\Omega$ typical, $100\,\Omega$ max

Insulation resistance: $>1000\text{M}\Omega/500\text{V}$ DC


3. Solderability

Vapor phase: 215°C, 30sec. Max

4.Environmental Characteristics

Operating temperature: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$

Operating humidity: 10%~+95%RH



3	COVER		1	PAGE	BLACK
2	PIN		32	C2680 T=0.8	Cu/5n Plated
1	HOUSING		1	ABS	BLACK
NO.	PART NAME		TERNO.	QTY	MATERIAL
					REMARK
DSND	JIANLINZ	DATE	2014.10.30	SCALE: 1:1	NAME:

CCTV 11 15 14		
CHKD	SHICANZHON	CAT.NO:
DATE	VIEW: 	
APVD	SHANHAICHEN	
DATE	2014.10.30	
UNIT:mm		

广东富盈兴业精密科技实业有限公司	DWG.NO.	REVISED
		A/0