








Rev.	ECN	Number	Description	Date	Drawn	Checkd	Approved



Notes:

- | | |
|---------------------------------------|--------|
| 1.1 Rated Voltage | 60V AC |
| 1.2 Frequency Range | 0~6GHz |
| 1.3 Impedance | 50W |
| 1.4 Operating Temperature | -40°C~ |
| 2.1 Voltage Standing Wave Ratio(VSWR) | |
| 1.3 max. at | 0~3GHz |

2.2 Durability

1.4 max. at 3~6GHz
30 cycles

ITEM	PART NAME	Q'TY	MATERIAL / FINISH
C	CONTACT	1	COPPER ALLOY/GOLD PLATED OVER Ni
B	HOUSING	1	Hight Temp. Plastic UL94V-0/BLACK
A	SHELL	1	COPPER ALLOY/Au PLATED OVER Ni

BOM LIST

 深圳市玥达电子科技有限公司 Shenzhen Yueda Electronic Technology Co.,Ltd.	GENERAL TOLERANCE	SCALE: 1:1	DRAWN	DATE	DWG. NO.	TITLE CUSTOMER DRAWING USS REC CONN, H0.6 USS SERIES	REV. A	
	XX. ± 0.50							
	X. ± 0.35	X.° ± 2.0°	UNIT: mm	CHECK	DATE			
	.X ± 0.25	.X° ± 1.0°			PARTS NO.(INTENDED USE)			
	.XX ± 0.15	.XX° ± 0.5°	SIZE: A4	APPROVE	DATE	YDC-LCSP-04	BY	1/1