


1、Physical Dimensions(size of 1206)

Part Number	A		B		C		D	Unit:mm Marking
	Min	Max	Min	Max	Min	Max	Min	
K1206L075/8YR	3.00	3.40	1.40	1.80	0.45	0.85	0.25	T07



2、Electrical Characteristics

Part Number	I _H (A)	I _T (A)	V _{max} (V)	I _{max} (A)	T _{trip} (Max time to trip)		P _d typ (W)	R _{min} (Ω)	R _{1max} (Ω)
	Current(A)	Time(S)							
K1206L075/8YR	0.75	1.50	8	100	8.00	0.10	0.40	0.100	0.400

I_H: Holding Current: maximum current at which the device will not trip in 25°C still air.

I_T: Tripping Current minimum current at which the device will trip in 25°C still air.

V_{max}: Maximum voltage device can withstand without damage at rated current.

I_{max}: Maximum fault current device can withstand without damage at rated voltage.

T_{trip}: Maximum time to trip(s) at assigned current.

P_d typ: Rated working power.

R_{min}: Minimum resistance of device prior to trip at 25°C.



R_{1max}: Maximum resistance of device is measured one hours post reflow at 25°C.

Noted: All electrical function test is conducted after PCB mounted.

3、Thermal Derating

K1206L075/8YR	Maximum ambient operating temperature								
	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
Hold Current(A)	1.11	1.00	0.85	0.75	0.67	0.61	0.52	0.50	0.42
Trip Current(A)	2.22	2.00	1.70	1.50	1.34	1.22	1.04	1.00	0.84

4、Solder Reflow Recommendations



Notes: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

5、Package Information

Packing quantity: 4000CS/Reel

Note: Reel packaging per EIA-481-1 standard