SM0355S6RL

-30V/-5.5A P-Channel MOSFET

Features

- Trench Power MV MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low $R_{DS(ON)}$

Product Summary

V_{DS}	$R_{DS(ON)}$ MAX	I_D MAX
-30V	58mΩ@-10V	-5.5A
	88mΩ@-4.5V	

Application

- DC-DC Converters
- Power management functions





Schematic diagram

Absolute Maximum Ratings (TA=25℃unless otherwise noted)

Symbol	Parameter		Rating	Unit
Common Ratings (TC=25°C Unless Otherwise Noted)				
V_{DS}	Drain-Source Breakdown Voltage		-30	V
V_{GS}	Gate-Source Voltage		±20	V
T_J	Maximum Junction Temperature		150	°C
T_{STG}	Storage Temperature Range		-50 to 155	°C
I_S	Diode Continuous Forward Current	Tc=25°C	-5	A
Mounted on Large Heat Sink				
I_{DM}	Pulse Drain Current Tested	Tc=25°C	-23	A
I_D	Continuous Drain Current	Tc=25°C	-5.5	A
P_D	Maximum Power Dissipation	Tc=25°C	1.9	W
$R_{\theta JA}$	Thermal Resistance Junction-Ambien		65	°C/W

Electrical Characteristics (TJ=25℃ unless otherwise noted)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
$BV_{(BR)DSS}$	Drain-Source Breakdown Voltage	V_{GS}=0V, I_D=-250μA	-30	--	--	V
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS}=-30V, V_{GS}=0V	--	--	-1	μA
I_{GSS}	Gate-Body Leakage Current	V_{GS}=±20V, V_{DS}=0V	--	--	±100	nA
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS}=V_{GS}, I_D=-250μA	-1.0	-1.5	-2.5	V
$R_{DS(on)}$	Drain-Source On-State Resistance	V_{GS}=-10V, I_D=-5A	--	40	60	mΩ
		V_{GS}=-4.5V, I_D=-4A	--	56	90	mΩ
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
C_{ISS}	Input Capacitance	V_{DS}=-15V, V_{GS}=0V, f=1MHz	--	520	--	pF
C_{OSS}	Output Capacitance		--	130	--	pF
C_{RSS}	Reverse Transfer Capacitance		--	70	--	pF
Switching Characteristics						
Q_g	Total Gate Charge	V_{DS}=-15V, I_D=-5A, V_{GS}=-10V	--	12	--	nC
Q_{gs}	Gate Source Charge		--	2	--	nC
Q_{gd}	Gate Drain Charge		--	2.9	--	nC
$t_{d(on)}$	Turn-on Delay Time	V_{DS}=-15V, I_D=-5A, V =-10V, R_G=3Ω	--	7	--	nS
t_r	Turn-on Rise Time		--	13	--	nS
$t_{d(off)}$	Turn-Off Delay Time		--	14	--	nS
t_f	Turn-Off Fall Time		--	9	--	nS
Source- Drain Diode Characteristics						
V_{SD}	Forward on voltage	Tj=25℃, Is=-5A	--	--	-1.2	V

Typical Operating Characteristics



V_{DS}, Drain -Source Voltage (V)

Fig1. Typical Output Characteristics



Qg -Total Gate Charge (nC)

Fig2. Typical Gate Charge Vs.Gate-Source Voltage



Tj - Junction Temperature (°C)

Fig3. Normalized On-Resistance Vs. Temperature



- I_D, Drain-Source Current (A)

Fig4. On-Resistance Vs. Drain-Source Current



$-V_{DS}$, Drain -Source Voltage (V)

Fig5. Maximum Safe Operating Area



$-V_{DS}$, Drain-Source Voltage (V)

Fig6 Typical Capacitance Vs.Drain-Source Voltage

SOT-89-3L Package information



Symbol	Dimensions in Millimeters(mm)		Dimensions in Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF		0.061 REF	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP		0.060 TYP	
e1	3.000 TYP		0.118 TYP	
L	0.900	1.200	0.035	0.047