


DATA SHEET

2N7002KM


- ◇ High Density Cell Design for Low RDS(ON)
- ◇ Voltage Controlled Small Signal Switch
- ◇ Small Outline Surface Mount Package
- ◇ RoHS compliant / Green EMC

Device Marking Code	
2N7002KM	RK

Circuit Diagram



SOT723



MAXIMUM RATINGS (Ta=25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	± 20	V
V_{EB0}	Emitter-Base Voltage	6	V
I_D	Drain Current-Continuous	0.34	A
P_D	Power Dissipation	0.15	W
$R_{\theta JA}$	Thermal Resistance From Junction To Ambient	833	°C/W
T_j	Junction Temperature	150	°C
T_{stg}	Storage Temperature	-55~+150	°C

ELECTRICAL CHARACTERISTICS @ 25° C Unless Otherwise Specified

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	60			V
$V_{GS(th)}$	Gate-Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	1.0	1.4	2.5	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=48V, V_{GS}=0V$			1.0	μA
I_{GSS}	Gate-Body Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$			± 10	μA
		$V_{GS}=\pm 10V, V_{DS}=0V$			± 200	nA
		$V_{GS}=\pm 5V, V_{DS}=0V$			± 100	nA

$R_{DS(on)}$	Drain-Source On-Resistance	$V_{GS}=10V, I_D=500mA$		1.3	4.0	Ω
		$V_{GS}=4.5V, I_D=200mA$		1.4	4.5	
Q_r	Recovered Charge	$V_{GS}=0V, I_S=300mA, V_R=25V$ $dl/dt=-100A/\mu s$		30		nC
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{DS}=10V, V_{GS}=0V, f=1MHz$			40	pF
C_{oss}	Output Capacitance				30	
C_{rss}	Reverse Transfer Capacitance				10	
Switching Characteristics						
$t_{d(on)}$	Turn-on Delay Time	$V_{DD}=25V, V_{GS}=10V, R_L=250\Omega,$ $R_{GS}=50K, R_{GEN}=25\Omega$			10	nS
$t_{d(off)}$	Turn-off Delay Time				15	
t_{rr}	Reverse Recovery Time	$V_{GS}=0V, I_S=300mA, V_R=25V,$ $dl/dt=-100A/\mu s$		30		
Source-Drain Diode Characteristics						
V_{SD}	Diode Forward Voltage	$V_{GS}=0V, I_S=200mA$		0.97	1.5	V

Curve Characteristics

Fig. 1 - Output Characteristics




Fig. 2 - Transfer Characteristics




Fig. 3 - $R_{DS(ON)} - I_D$




Fig. 4 - $R_{DS(ON)} - V_{GS}$




Fig. 5 - $I_S - V_{SD}$






Fig. 6 - Threshold Voltage



ORDERING INFORMATION

Device	Package	Shipping	Tape wide	Emboss pitch	Tape specification	Notes
2N7002KM	SOT723	Tape & Reel 8000pcs /7" Reel	8mm	4mm	Conductive	

PACKAGE DIMENSIONS



NOTICE

POPPULA'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS COMPONENTS IN ANY LIFE SUPPORT DEVICES OR SYSTEMS.

POPPULA reserve the right to make modifications, enhancements improvements corrections or other changes without further notice to any product herein. POPPULA does not assume any liability arising out of the application or use of any product described herein.