


6


PRODUCT NUMBER	SIZE	LATCHING AVAILABILITY	MISSING PIN POSITIONS
71922-X06(Z)LF	2x3	0/1/2	
71922-X08(Z)LF	2x4	0/1/2	
71922-X10(Z)LF	2x5	0/1/2	
71922-X14(Z)LF	2x7	0/1/2	
71922-X16(Z)LF	2x8	0/1/2	
71922-X18(Z)LF	2x9	0/1/2	
71922-X20(Z)LF	2x10	0/1/2	
71922-X26(Z)LF	2x13	0/1/2	
71922-X28(Z)LF	2x13	0/1/2	PIN 5 TO 12
71922-X30(Z)LF	2x15	0/1/2	
71922-X34(Z)LF	2x17	0/1/2	
71922-X35(Z)LF	2x17	0/1/2	PIN 2 & 3
71922-X39(Z)LF	2x20	0/1/2	PIN 20
71922-X40(Z)LF	2x20	0/1/2	
71922-X44(Z)LF	2x22	0/1/2	
71922-X50(Z)LF	2x25	0/1/2	
71922-X60(Z)LF	2x30	0/1/2	
71922-X64(Z)LF	2x32	0/1/2	

PLATING :


- 0.76µm GOLD/GXT
(PdNi WITH GOLD FLASH) ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
UNDERPLATE : 1.27µm Ni MIN



LATCHING FEATURES:



1= STANDARD LATCH



2= LOW PROFILE LATCH

mat'l. code				surface		tolerance		projection	product family		
NOTES 1, 2				ISO 1302		ISO 406		ISO 1101	QUICKIE HEADER		
ltr	ecn no	dr	date	tolerances unless otherwise specified					title		
V	F-54576	DDE	25.02.10	angles		linear			SHR.EL.HEADER		
						.x ± 0.3		mm			
						.xx ± 0.13					
P	F08-0146	YOV	08.04.11			xxx ± 0.05		scale 2:1			
R	B-16776	LMU	14.01.23	dr	D.LEGRAND	01.01.24			dwg no		
S	B-19092	LMU	14.10.16	engr	J.COMPAGNON	01.01.24			sheet 2 of 2		
T	B-20349	BVE	15.03.02	chr	JF.NOTTEAU	01.01.24			size		
U	F-49503	LMU	23.10.17	appd	J.COMPAGNON	01.01.24			A3		
sheet				revision					type		
index				sheet					CUSTOMER Drawing		