



清远市震东电子科技有限公司

一体成型电感性能尺寸标准

受控

文件名称	制造标准	文件编号	WI-R&D-050	生效日期	2024/ 12/5	版本号A0	页码	1月11日
1.尺寸(单位:mm)								
Series	A	B	C	D	E	I Typ	J Typ	H Typ
ZD1265	12.6±0.3	13.45±0.35	6.5 Max	2.0±0.5	3.8±0.3	3.25	8.0	5.5
2. 产品编号	电感	DCR	饱和电流			温升电流		
	@100KHZ, 1V	Max.	Max	Typ.		Max	Typ.	
单位	μ	mΩ	A			A		
项目	L	DCR	Isat			Irms		
ZD1265-4R7M	4.7±20%	9.0	/	24.0		/	16.0	
ZD1265-5R6M	5.6±20%	12.0	/	22.5		/	14.0	
ZD1265-6R8M	6.8±20%	13.0	/	19.0		/	13.0	
ZD1265-100M	10±20%	16.5	/	13.0		/	11.0	
ZD1265-150M	15±20%	26.0	/	11.0		/	9.5	
ZD1265-220M	22±20%	42.0	/	9.0		/	8.0	
ZD1265-330M	33±20%	65.0	/	8.0		/	6.5	
ZD1265-470M	47±20%	70.0	/	6.8		/	5.5	
ZD1265-680M	68±20%	105.0	/	5.2		/	4.8	
ZD1265-820M	82±20%	135.0	/	4.5		/	4.0	
ZD1265-101M	100±20%	170.0	/	4.0		/	3.5	
3.1. 包装尺寸 (单位: mm)								
								
3.2 每卷包装数量:								
规格系列	卷盘尺寸							
ZD1265	A	B	C		E			
	330±2.0	100+0.5/-0.2	13.4+0.3/-0.4		24.4+2.0/-0			
	载带尺寸							
	W	P	P0	K0	T	A0	B0	
	24.0±0.3	16.0±0.1	4.0±0.1	6.8±0.1	0.40±0.05	13.1±0.1	14.4±0.1	